

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0039000286](#)
Status: **Active**
Overview: [KK Interconnect Systems](#)
Description: [KK 396 Crimp Terminal 2478, 18-24 AWG, Reel, Brass, 0.9µm Pre-Plated Tin \(Sn\)](#)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification PK-2759-002-001 \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	2478
Application	Power, Wire-to-Board
Crimp Quality Equipment	Yes
Overview	KK Interconnect Systems
Packaging Alternative	39000344 (Loose)
Product Name	KK 396, KK 508
Taxonomy	Crimp Terminals
UPC	800753334984

Physical

Durability (mating cycles max)	25
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.152/g
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.889µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.30-2.50mm
Wire Size AWG	18, 24
Wire Size mm ²	0.21-0.82

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Engineering Number	2478T
--------------------	-------

Reference - Drawing Numbers

Crimp Specification	CS-2478-001, CS-2478-002
Packaging Specification	PK-2759-002-001
Sales Drawing	SD-2478X-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[2478 Series](#)

Use With

[2574](#) , [2139](#) , [41695](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
-------------	-----------

Extraction Tool for Flat Blade, 3.96mm KK, 2.00mm, 3.96mm EdgeMate, and Ultra- Fit Terminals Hand Crimp Tool for 3.96mm Pitch KK Crimp Terminals, 18-24 AWG	11030016
--	--------------------------

Mini-Mac Applicator [638885000](#)
for KK and Trifurcon,
3.96mm Terminals,
18-24 AWG, check
ATS for Wire
Insulation Diameter
Compatibility

Japan

Description	Product #
--------------------	------------------

Hand Extraction Tool	11260059
----------------------	--------------------------

Applicator for M211A	11260092
----------------------	--------------------------

Bench Press, 18-28

AWG Wire

Hand Extraction Tool	570926000
----------------------	---------------------------

This document was generated on 10/12/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION