

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [130110-0043](#)  
**Status:** **Active**  
**Description:** Super-Safeway™ 500W Twin Halogen Floodlight Stanchion Mount with Switch, Cord Type 12/3 SOOW, Cord Length 0.457m

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR85374

**General**

|                    |                        |
|--------------------|------------------------|
| Product Family     | Portable Lighting      |
| Series             | <a href="#">130110</a> |
| NEMA Configuration | NEMA 5-20              |
| NEMA Rating        | Rain Tight             |
| Outlet             | Side                   |
| Product Name       | Super-Safeway™         |
| Type               | Wide Area Lamps        |
| Woodhead           | Yes                    |

**Physical**

|                         |                             |
|-------------------------|-----------------------------|
| Cord Length - Primary   | 0.457m                      |
| Cord Length - Secondary | N/A                         |
| Depth                   | 1.16m                       |
| Duty                    | Industrial                  |
| Guard Included          | No                          |
| Guard Type              | N/A                         |
| Height                  | 2.29m                       |
| Length                  | 1.16m                       |
| Material - Globe        | Tempered Glass              |
| Material - Guard        | #10 Gauge Zinc-plated Steel |
| Mounting Style          | Stanchion                   |
| Packaging Type          | Carton                      |
| Socket Construction     | N/A                         |

**Electrical**

|                             |                |
|-----------------------------|----------------|
| Bulb Type                   | Quartz Halogen |
| Cord Type - Primary         | 16/3 SOOW      |
| Lamp Type                   | T-3 RSC        |
| Lamp Wattage - Maximum      | 500W           |
| Lumens                      | 9200           |
| On/Off Switch               | Yes            |
| Voltage (Fixture) - Maximum | 120VAC 60 HZ   |

**Material Info**

|                 |             |
|-----------------|-------------|
| Old Part Number | SBS2500     |
| UPC             | 78678801180 |



**EU RoHS**

**Not RoHS Compliant**  
**REACH SVHC**  
**Not Reviewed**  
**Low-Halogen Status**  
**Not Reviewed**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

130110Series