


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0510670300**
Status: **Active**
Overview: Mighty-SPOX Connector System
Description: Mighty-SPOX Wire-to-Wire and Wire-to-Board Housing, 3.50mm Pitch, Positive Lock, 3 Circuits, Natural



Documents:

3D Model	Product Specification PS-51067-016-001 (PDF)
3D Model (PDF)	Product Specification PS-51067-017-001 (PDF)
Drawing (PDF)	Product Specification PS-51067-018-001 (PDF)
Product Specification PS-51067-001-001 (PDF)	Product Specification PS-51067-019-001 (PDF)
Product Specification PS-51067-002-001 (PDF)	Product Specification PS-51067-021-001 (PDF)
Product Specification PS-51067-003-001 (PDF)	Product Specification PS-51067-022-001 (PDF)
Product Specification PS-51067-004-001 (PDF)	Product Specification PS-54111-001-001 (PDF)
Product Specification PS-51067-005-001 (PDF)	Product Specification PS-54452-006-001 (PDF)
Product Specification PS-51067-006-001 (PDF)	Packaging Specification SPK-51067-001-001 (PDF)
Product Specification PS-51067-007-001 (PDF)	Packaging Specification SPK-51067-001-002 (PDF)
Product Specification PS-51067-008-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	<u>51067</u>
Application	Power, Wire-to-Board, Wire-to-Wire
Overview	<u>Mighty-SPOX Connector System</u>
Product Name	Mighty-SPOX
Taxonomy	Connector Housings
UPC	800753574373

Physical

Circuits (maximum)	3
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Material - Resin	Polyester
Net Weight	694.500/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.50mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

Material Info

Reference - Drawing Numbers

Packaging Specification	SPK-51067-001-001, SPK-51067-001-002
Product Specification	PS-51067-001-001, PS-51067-002-001, PS-51067-003-001, PS-51067-004-001, PS-51067-005-001, PS-51067-006-001, PS-51067-007-001, PS-51067-008-001, PS-51067-016-001, PS-51067-017-001, PS-51067-018-001, PS-51067-019-001,

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

51067 Series

Mates With

51114 , 53258 , 53259 , 53265 , 53266

Use With

50217 Crimp Terminals

Sales Drawing

PS-51067-021-001, PS-51067-022-001,
PS-54111-001-001, PS-54452-006-001
SD-51067-XX00-001

This document was generated on 09/01/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION