

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0638116800](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: PremiumGrade Hand Crimp Tool for MLX Pin and Socket Terminals, 14-20 AWG

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Application Tooling
Series	207129
Comments	Field Repair, See Tooling Specification (PDF) Above; Type: 2C
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	PremiumGrade
Taxonomy	Crimp Presses and Crimp Hand T
Tool Type	Hand Crimp Tool
UPC	822350856355
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight 576.034/g

Material Info

Reference - Drawing Numbers

Application Tooling Documents
ATS-6381168HM-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Not Relevant

Not Relevant

Not Contained

Search Parts in this Series

[207129 Series](#)

Use With

Loose Piece Terminals

Application Tooling | [FAQ](#)

Description	Product #
-------------	-----------

MLX Female Crimp Terminal 42024, 14-20 AWG, Reel, Brass, Tin (Sn) Plating	2081001
---	-------------------------

MLX Crimp Terminal 42024, 14-20 AWG, Bag Tin (Sn)	2081002
---	-------------------------

MLX Female Crimp Terminal 42024, 14-20 AWG, Reel, Phosphor Bronze, Tin (Sn) Plating	2081003
---	-------------------------

MLX Crimp Terminal 42024, 14-20 AWG, Bag Tin (Sn)	2081004
---	-------------------------

MLX Male Crimp Terminal 42023, 14-20 AWG, Reel, Brass, Tin (Sn) Plating	<u>2082003</u>
MLX Crimp Terminal 42023, 14-20 AWG, Bag Tin (Sn)	<u>2082004</u>
MLX Male Crimp Terminal 42023, 14-20 AWG, Reel, Phosphor Bronze, Tin (Sn) Plating	<u>2082005</u>
MLX Crimp Terminal 42023, 14-20 AWG, Bag Tin (Sn)	<u>2082006</u>

This document was generated on 10/11/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION