

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936011531

Status:

Active

Overview:


GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect STD - Standard, Single Lever Surface Mount Housing, Die-cast Aluminum, with 1 Lever, with Cover, with Gasket, Size 10B «57x27», Pg16 Thread, Grey

|                               |                                                      |
|-------------------------------|------------------------------------------------------|
| Documents:                    |                                                      |
| <a href="#">Drawing (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a> |

|                             |                                                         |
|-----------------------------|---------------------------------------------------------|
| Agency Certification        |                                                         |
| CSA                         | 256883                                                  |
| UL                          | E249674                                                 |
| General                     |                                                         |
| Product Family              | Industrial Connectors / Enclosures                      |
| Series                      | 93601                                                   |
| Component Size              | 10B «57X27»                                             |
| Component Type              | Single Lever SMT Housing                                |
| IP Rating                   | IP66                                                    |
| Overview                    | GWconnect Heavy Duty Connectors (HDC)                   |
| Product Category            | Heavy Duty Connectors                                   |
| Product Name                | GWconnect                                               |
| Standard                    | ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984 |
| Taxonomy                    | Heavy-Duty Connectors                                   |
| Type                        | STD                                                     |
| UPC                         | 887191826868                                            |
| Physical                    |                                                         |
| Cover Coating               | Polyester Powder                                        |
| Cover Color                 | Grey RAL 7037                                           |
| Housing Coating             | Polyester Powder                                        |
| Housing Color               | Grey RAL 7037                                           |
| Lock to Mating Part         | Yes                                                     |
| Material - Cover            | Die-cast Aluminum                                       |
| Material - Gasket           | NBR                                                     |
| Material - Housing          | Die-cast Aluminum                                       |
| Material - Lever            | Galvanized Steel                                        |
| Mounting Style              | Surface Mount                                           |
| Net Weight                  | 290.960/g                                               |
| Number of Levers            | 1                                                       |
| Packaging Type              | Bag                                                     |
| Thread Size                 | Pg16                                                    |
| Thread Type                 | (Pg)                                                    |
| Electrical                  |                                                         |
| Voltage - Maximum           | 500V                                                    |
| Material Info               |                                                         |
| Engineering Number          | 7810.6313.0                                             |
| Reference - Drawing Numbers |                                                         |
| Sales Drawing               | 936011555-000                                           |



|                                                               |                           |
|---------------------------------------------------------------|---------------------------|
| EU ELV                                                        |                           |
| Not Relevant                                                  |                           |
| EU RoHS                                                       | China RoHS                |
| Compliant                                                     |                           |
| REACH SVHC                                                    |                           |
| Not Contained Per - D(2022)4187-DC (10 June 2022)             |                           |
| Halogen-Free                                                  |                           |
| Status                                                        |                           |
| Low-Halogen                                                   |                           |
| For more information, please visit <a href="#">Contact US</a> |                           |
| China ROHS                                                    | Green Image               |
| ELV                                                           | Not Relevant              |
| RoHS Phthalates                                               | Not Contained             |
| ZZCERT_CE - Declaration of Conformity                         | CER_4000400719_00_000.pdf |

Search Parts in this Series

93601 Series

Use With

Size 10B «57x27» S-D, S-DD, S-E, S-EE, S-EP, S-ES, S-HSB, S-ESHV, S-K, S-M, and S-EHV Inserts