


172258 -1 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



172258 -1

[Active](#)

DLI Connectors

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Connector
- ? Connector Type = Header (Cap)
- ? Number of Positions = 16
- ? Phosphor Bronze Contact Material
- ? Selective Tin Contact Mating Area Plating Material

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [16P CAP HOUSING ASSY \(V -TYPE\) DUAL LINE INTERLOCK CO...](#) (TIF, Japanese)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? [Dual Line Interlock Connector](#) (TIF, English)

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Connector
- ? [Connector Type](#) = Header (Cap)
- ? [Number of Positions](#) = 16
- ? [PCB Mount Angle](#) = Vertical
- ? Post Size (mm [in]) = 0.64 [.025]

Body Related Features:

- ? [Lock Plate/Double Lock Plate](#) = Double Lock Plate
- ? Number of Rows = 2
- ? Row Spacing (mm [in]) = 4.60 [0.818]

Contact Related Features:

- ? [Contact Material](#) = Phosphor Bronze
- ? [Contact Mating Area Plating Material](#) = Selective Tin
- ? Contact Centerline Spacing (mm [in]) = 3.00 [0.118]
- ? Contact Shape = Square

Housing Related Features:

- ? Housing Material = Nylon
- ? Housing Color = Black
- ? Housing Flammability Rating = UL 94V -2

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- ? [Terminate To](#) = Printed Circuit Board

Packaging Related Features:

- ? [Packaging Method](#) = Loose Piece

Other:

- ? Brand = Tyco Electronics