

## 1838250 - 3 Product Details

**Live Product Chat** US Only  
 8:30am - 5pm ET, Mon - Fri



**1838250 - 3**

[Active](#)

### M8/M12 Connector System

[Always EU RoHS/ELV Compliant](#) ( [Statement of Compliance](#) )

#### Product Highlights:

- ? Lead Assembly
- ? Lead Assembly Type = Cable
- ? Wire Size = 0.34 (22 AWG) mm <sup>2</sup> [AWG]
- ? Number of Positions = 4
- ? Cable Length = 5.00 M

[View all Features](#) | 
 [Find Similar Products](#)

#### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- ? [M12 RIGHT ANGLED MALE CONNECTOR 4 POSITION, PVC CABLE](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- ? None Available

#### Product Specifications:

- ? None Available

#### Application Specifications:

- ? None Available

#### Instruction Sheets:

- ? None Available

#### CAD Files:

- ? None Available

#### Additional Information:

- ? [Product Line Information](#)

#### Related Products:

- ? [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- ? [Product Type](#) = Lead Assembly
- ? [Wire Size \(mm <sup>2</sup> \[AWG\]\)](#) = 0.34 (22 AWG)
- ? [Number of Positions](#) = 4
- ? Insulation Material = PVC
- ? Shielded = No
- ? Thread Size = M12
- ? Gender = Male
- ? Mount Angle = Right Angle

#### Mechanical Attachment:

- ? Panel Mount = No

#### Body Related Features:

- ? [Lead Assembly Type](#) = Cable
- ? [Cable Length \(M \[ft\]\)](#) = 5.00 [16.404]
- ? Cable Color = Black
- ? Connector Color = Black
- ? Wire Color = Brown, White, Blue, Black
- ? [LED](#) = Without

#### Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

#### Packaging Related Features:

- ? Packaging Quantity = 20

#### Other:

- ? Brand = Tyco Electronics