



General Information

Kit Part Number:	1-2110856-1
Description:	JC6 Series Quick Connect Dual-Barrier Strip with Wire Clamping Screws and Hardware Kit
Application:	HVAC/R Systems, Industrial Automation, Industrial Controls, Irrigation, Machine Tools, Power Supplies, Security, Transformers
Family:	Dual-Barrier Strip
TE Brand:	BUCHANAN Products
Solution:	Field Wiring
Product Type:	Dual-Barrier
Number of Pieces:	14
RoHS:	Yes

Specifications

Circuit Size(s):	2, 3, 4, 5, 6, 8, 10
Current Rating:	5A
Mounting Style:	Quick Connect
Pitch:	0.375"
Terminal Type:	Wire Clamping Screws
Tool Included:	No
Voltage Rating:	600V
Wire Gauge (AWG):	22-12

Product Highlights

Dual-Barrier Blocks help contain stray or frayed wire ends. This helps prevent electrical shorts - not only between positions on the same block, but also between other components immediately adjacent to the block. The Dual-Barrier design provides a more cost-effective solution than the Tri-Barrier Strips while still supplying many of the design advantages.

Features and Benefits

- Fast Wiring - backed out wire ready screws
- Interrupted thread designed to prevent screws from falling out
- Standoffs allow flux and solvents to drain during cleaning
- Molded-to-Length or Cut-to Length Versions available

Applications

- Industrial Controls and Automation
- Machine Tools
- HVAC/R
- Power Supplies
- Security/Irrigation
- Transformers



Bill of Materials

Part No.	Qty In Kit	Description	Datasheet	P/N Details	Search Distributors Inventory
1546842-2	2	0.375" Pitch, 2 Circuit Dual-Barrier Strip, 0.250" Quick Con...	Datasheet	Details	Search
5-1437665-0	2	0.375" Pitch, 3 Circuit Dual-Barrier Strip, 0.250" Quick Con...	Datasheet	Details	Search
1546842-4	2	0.375" Pitch, 4 Circuit Dual-Barrier Strip, 0.250" Quick Con...	Datasheet	Details	Search
1546842-5	2	0.375" Pitch, 5 Circuit Dual-Barrier Strip, 0.250" Quick Con...	Datasheet	Details	Search
1546842-6	2	0.375" Pitch, 6 Circuit Dual-Barrier Strip, 0.250" Quick Con...	Datasheet	Details	Search
1546842-8	2	0.375" Pitch, 8 Circuit Dual-Barrier Strip, 0.250" Quick Con...	Datasheet	Details	Search
1-1546842-0	2	0.375" Pitch, 10 Circuit Dual-Barrier Strip, 0.250" Quick Co...	Datasheet	Details	Search

Recommended Tool

Part No.

Included in Kit



