

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1721590607](#)
Status: **Active**
Overview: [EdgeMate Wire-to-Edge-Card Power Connector](#)
Description: 3.96mm Pitch EdgeMate Wire-to-Board Edge Card Connector, Female, Nylon 6/6, White, UL94-V2, with Positive Lock, 7 Circuits

Documents:

3D Model	Product Specification PS-172160-0001-001 (PDF)
Drawing (PDF)	Packaging Specification PK-172159-0001-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

UL E29179

General

Product Family	Edge Card Connectors
Series	172159
Comments	See Product Specification for maximum current rating by wire AWG and terminal material.
Component Type	Edgecard to Wire
Data Rate	Unrated
Edge Card Thickness	N/A
High Power Bay (30.0A or more)	No
Orientation	Right-Angle
Overview	EdgeMate Wire-to-Edge-Card Power Connector
Product Name	EdgeMate
Standard Based	General
UPC	887191569949

Physical


(p)ower-(s)ignal Configuration	7p - 0s
Circuit Size Range	1-64 Circuits
Circuits (Loaded)	7
Circuits (maximum)	7
Color - Resin	White
Durability (mating cycles max)	25
Entry Angle	90° Angle
Flammability	94V-2
Keying to Mating Part	Yes
Material - Plating Mating	N/A
Material - Resin	Nylon
Net Weight	2.880/g
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.57mm
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.96mm
Polarized to Mating Part	Polarizing Ribs
Temperature Range - Operating	-40° to +105°C, -40° to +80°C
Termination Interface: Style	Straddle Mount-Edge Card

Electrical

Current - Maximum per Contact	7.0A
Voltage - Maximum	250V

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[172159](#) Series

Mates With

Edge Card PCB

Use With

[172160](#)

Material Info

Reference - Drawing Numbers

Packaging Specification
Product Specification
Sales Drawing

PK-172159-0001-001
PS-172160-0001-001
SD-172159-0002-000

This document was generated on 03/02/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION