



## SLC40AB-1006A Product Details

[Share](#) | [Print](#) | [Email](#)


SLC40AB-1006A

TE Internal Number: CX5691-000

 **Active**

### Braid, Fixed, Spin and Tinel Lock Adapters

[Not EU RoHS or ELV Compliant](#)

#### Product Highlights:

- Applies To Cable
- Style = Raychem Spinlock Variable Angle Backshells
- Connector Code = 40
- 45°, 90°, Straight
- Shell Size = 10

[View all Features](#)

#### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)
 [Request Sample](#)
 [Find Similar Products](#)
 [Buy Product](#)

#### Documentation & Additional Information

##### Product Drawings:

- [Spin-Lock Adapter Saddle Clamp, Code 40](#) (PDF, English)

##### Catalog Pages/Data Sheets:

- None Available

##### Product Specifications:

- None Available

##### Application Specifications:

- None Available

##### Instruction Sheets:

- None Available

##### CAD Files:

- None Available

##### Related Products:

- [Tooling](#)

[List all Documents](#)

#### Product Features (Please use the Product Drawing for all design activity)

##### Product Type Features:

- [Style](#) = Raychem Spinlock Variable Angle Backshells
- [Angle](#) = 45°, 90°, Straight
- [Shell Size](#) = 10
- Finish = Cadmium over Nickel
- Material = Aluminum

##### Electrical Characteristics:

- [Entry Diameter \(mm \[in\]\)](#) = 9.50 [0.380]
- Manufacturer = Raychem
- Finish Code = B
- Tinel-Lock Ring Supplied = TR06AI

##### Body Features:

- [Connector Code](#) = 40
- [Entry Size](#) = 6
- [Cable Diameter \(Max.\) \(mm \[in\]\)](#) = 3.89 - 5.94 [0.153 - 0.234]

##### Configuration Features:

- Material Code = A

##### Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process

##### Conditions for Usage:

- Applies To = Cable

##### Other:

- Brand = Raychem

#### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

#### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

#### Customer Support

[Email or Chat With Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage your Account](#)

#### Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

