

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5052702012

Status:

Active

Overview:

SlimStack Board-to-Board/Board-to-FPC Connectors

Description:

SlimStack Board-to-Board Receptacle, 0.35mm Pitch, SSB RP Series, 0.70 or 0.80mm Mated Height, 2.00mm Mated Width, 20 Circuits, Armor Nail

- Documents:
- 3D Model

Packaging Specification 5052709200SPK-200 (PDF)
- Drawing (PDF)

Datasheet (PDF)
- 3D Model (PDF)

Product Guide (PDF)
- Product Specification 5052700001-PS-000 (PDF)

RoHS Certificate of Compliance (PDF)
- Product Specification 5052700003-PS-000 (PDF)

Reference Guide (PDF)
- Application Specification 5052700000-A01 (PDF)

General	
Product Family	PCB Receptacles
Series	505270
Application	Board-to-Board
Overview	SlimStack Board-to-Board/Board-to-FPC Connectors
Product Name	SlimStack
Series Name	0.35, SSB RP
Taxonomy	Board-to-Board Connectors
UPC	191128462006

Physical	
Circuits (Loaded)	20
Circuits (maximum)	20
Color - Resin	Black
Durability (mating cycles max)	30
Glow-Wire Capable	No
Mated Height	0.70mm, 0.80mm
Mated Width	2.00mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer
Net Weight	12.290/mg
Number of Rows	2
Orientation	Vertical
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.35mm
Pitch - Termination Interface	0.35mm
Plating min - Mating	0.100µm
Plating min - Termination	0.050µm
Polarized to Mating Part	No
Polarized to PCB	No
Temperature Range - Operating	-40° to +85°C
Termination Interface: Style	Surface Mount

Electrical	
Current - Maximum per Contact	0.3A, 3.0A
Voltage - Maximum	50V AC (RMS)/DC

Material Info

Reference - Drawing Numbers



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

505270 Series

Mates With

SlimStack SSB RP Plug 505070 , 505274

Application Specification	5052700000-A01
Packaging Specification	5052709200SPK-200
Product Specification	5052700001-PS-000, 5052700003-PS-000
Sales Drawing	5052700001-SD-000, 5052701001-SD-000

This document was generated on 10/26/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION