

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5052741612](#)
Status: **Active**
Overview: SlimStack Board-to-Board/Board-to-FPC Connectors
Description: SlimStack Board-to-Board Plug, 0.35mm Pitch, SSB RP Series, 0.80 or 0.90mm Mated Height, 2.00mm Mated Width, 16 Circuits, Armor Nail, 0.15mm Fitting Nail Width

Documents:

3D Model	Packaging Specification 5052749200SPK-200 (PDF)
3D Model (PDF)	Datasheet (PDF)
Drawing (PDF)	Product Guide (PDF)
Product Specification 5052700001-PS-000 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification 5052700000-A01 (PDF)	Reference Guide (PDF)

General

Product Family	PCB Headers
Series	505274
Application	Board-to-Board
Overview	SlimStack Board-to-Board/Board-to-FPC Connectors
Product Name	SlimStack
Series Name	0.35, SSB RP
Taxonomy	Board-to-Board Connectors
UPC	191128462112

Physical

Breakaway	No
Circuits (Loaded)	16
Circuits (maximum)	16
Color - Resin	Black
Durability (mating cycles max)	30
Glow-Wire Capable	No
Mated Height	0.80mm, 0.90mm
Mated Width	2.00mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer
Net Weight	6.580/mg
Number of Rows	2
Orientation	Vertical
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.35mm
Pitch - Termination Interface	0.35mm
Plating min - Mating	0.100µm
Plating min - Termination	0.050µm
Polarized to Mating Part	No
Polarized to PCB	No
Temperature Range - Operating	-40° to +85°C
Termination Interface: Style	Surface Mount

Electrical

Current - Maximum per Contact	0.3A, 3.0A
Voltage - Maximum	50V AC (RMS)/DC

Material Info

Reference - Drawing Numbers



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[505274 Series](#)

Mates With

SlimStack SSB RP Receptacle [505270](#)

Application Specification
Packaging Specification
Product Specification
Sales Drawing

5052700000-A01
5052749200SPK-200
5052700001-PS-000
5052740001-SD-000, 5052741001-SD-000

This document was generated on 10/21/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION