


## 737094-2 Product Details

 **Live Product Chat** US Only  
8:30am - 5pm ET, Mon - Fri



**737094-2**

 [Active](#)

### CPC Connectors

[Converted to EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Connector Kit
- Number of Positions = 4
- Plug, Receptacle
- For Use With Socket and/or Pin Contacts
- Not Preloaded

[View all Features](#) | [Find Similar Products](#)

### Quick Links

[Check Pricing & Availability](#)  
[Search for Tooling](#)  
[View Mating Products \(4\)](#)  
[Product Feature Selector](#)  
[Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [KIT CONECTOR CPC, TAMANO 11 - 4 VIAS.](#) (TIF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version E)
- [3D Model](#) (IGES, Version E)
- [3D Model](#) (STEP, Version E)

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)
- [Mating Products \(4\)](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Product Type](#) = Connector Kit
- [Number of Positions](#) = 4
- [Gender](#) = Plug, Receptacle
- For Use With = Socket and/or Pin Contacts
- Termination Style = Wire
- [Shell Size](#) = 11
- [Shell Type](#) = All Plastic
- [Product Series](#) = Series 1
- [Thread Size](#) = 5/8 - 24 UNEF-2A
- [Sealed](#) = No
- Comment = Kit Contains Pins and Sockets

#### Mechanical Attachment:

- [Preloaded](#) = No
- [VDE Tested](#) = No

#### Termination Related Features:

- [Solder Tail Contact Plating](#) = Tin

#### Body Related Features:

- [Mount Style](#) = Free Hanging

#### Contact Related Features:

- [Contact Mating Area Plating](#) = Tin
- [Standard or Reverse Gender](#) = Standard
- Contact Material = Copper Alloy

#### Housing Related Features:

- Housing Material = Thermoplastic
- Housing Color = Black
- Housing Flammability Rating = UL 94V-0

#### Configuration Related Features:

- [Reverse Numbering](#) = Without

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Converted to comply with RoHS directive

#### Other:

- Brand = AMP