



# 1-1102359-1 Product Details

[Share](#) [Print](#) [Email](#)



**1-1102359-1**

TE Internal Number: 1-1102359-1

Active

## HTS Connectors and Accessories

Always EU RoHS/ELV Compliant (Statement of Compliance)

### Product Highlights:

- HB Series
- Accessory
- Accessory Type = Hood
- Product Size = 10
- Locking Device Type = Locking Clip at Housing Bottom

[View all Features](#)

### Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

## Documentation & Additional Information

### Product Drawings:

- None Available

### Catalog Pages/Data Sheets:

- [HTS Heavy Duty Connectors catalogue](#) (PDF, English)

### Product Specifications:

- None Available

### Application Specifications:

- None Available

### Instruction Sheets:

- None Available

### CAD Files:

- None Available

### Additional Information:

- [Product Line Information](#)

### Related Products:

- [Tooling](#)

[List all Documents](#)

Feedback

## Product Features (Please use the Product Drawing for all design activity)

### Product Type Features:

- Product Type = Accessory
- Accessory Type = Hood
- Product Size = 10
- [Thread Size](#) = PG29
- Finish = Silver Gray

### Body Features:

- Entry Style = Bottom - Cable-to-Cable
- Dimensions (L x H x W) (mm [in]) = 95.00 x 82.50 x 82.50 [3.740 x 3.248 x 3.248]
- Material = Die Cast Aluminum

### Contact Features:

- Corrosion Protected = No

### Configuration Features:

- Locking Device Type = Locking Clip at Housing Bottom

### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

### Packaging Features:

- Packaging Method = Loose Piece
- Packaging Quantity = 3

### Other:

- Series = HB
- Brand = HTS

## Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [AODA Accessibility Policy](#)
- [AODA Multi-Year Accessibility](#)

## Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

## Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

## Keep Me Informed



