




1217403-1 Product Details

[Share](#) [Print](#) [Email](#)


1217403-1

TE Internal Number: 1217403-1

Active

FASTON Uninsulated Receptacles & Housings

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Terminal
- Terminal Type = Receptacle
- Mating Area Interface Dimensions = 6.35 x 0.81 mm
- Board Mount = No
- Receptacle Style = Flag

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information	
Documents are temporarily unavailable. We are working hard to correct the problem. Please try again later.	Related Products: <ul style="list-style-type: none"> • Tooling

Product Features (Please use the Product Drawing for all design activity)	
<p>Product Type Features:</p> <ul style="list-style-type: none"> • Product Type = Terminal • Receptacle Style = Flag • Insulation Support = Insulation Support • Wire/Cable Type = Stranded • Insertion Force = Normal • Finish = Tin <p>Mechanical Attachment:</p> <ul style="list-style-type: none"> • Board Mount = No <p>Termination Features:</p> <ul style="list-style-type: none"> • Crimp Type = Tab-Lok <p>Dimensions:</p> <ul style="list-style-type: none"> • Mating Area Interface Dimensions (mm [in]) = 6.35 x 0.81 [.250 x .032] • Insulation Diameter (mm [in]) = 2.79 - 5.33 [.110 - .210] <p>Body Features:</p> <ul style="list-style-type: none"> • Weld Tab = Without • Wire Range (mm [AWG]) = 0.80-3.00² [18-12] • Material = Phosphor Bronze • Stock Thickness (mm [in]) = 0.45 [0.0175] 	<p>Contact Features:</p> <ul style="list-style-type: none"> • Terminal Type = Receptacle <p>Industry Standards:</p> <ul style="list-style-type: none"> • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Not relevant for lead free process • RoHS/ELV Compliance History = Always was RoHS compliant • UL Rating = Listed <p>Conditions for Usage:</p> <ul style="list-style-type: none"> • For Hermetic Header Tab = No <p>Packaging Features:</p> <ul style="list-style-type: none"> • Packaging Method = Strip <p>Other:</p> <ul style="list-style-type: none"> • Line = Premier • Brand = TE Connectivity

[Feedback](#)

Corporate Information About TE Investors News Room Supplier Portal Careers Terms & Conditions Privacy Policy AODA Accessibility Policy AODA Multi-Year Accessibility Plan	Quick Links Distributor Inventory Product Cross Reference Documents & Drawings Product Compliance Support Center Site Map	Customer Support Email or Chat With Us Find a Phone Number Knowledge Base Manage Your Account	Keep Me Informed
---	---	--	-----------------------------

