




225935-5 Product Details



225935-5

ARINC 600/404 Contacts and Accessories

Not EU RoHS or ELV Compliant

Product Highlights:

- Contact
- Contact Type = Pin
- Cable Type = RG 142A, RG 142B
- Applies To Coaxial Cable
- Gold (50) Contact Plating, Mating Area, Material

[View all Features](#)

Quick Links

- ▶ Pricing & Availability
- ▶ Search for Tooling
- ▶ Product Feature Selector
- ▶ Contact Us About This Product

TE Internal Number: 225935-5



[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- [AMP* ARINC 404 RACK-AND-PANEL CONNECTORS SERIES R, R... \(PDF, English\)](#)

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Feedback

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Contact
- [Cable Type](#) = RG 142A, RG 142B
- [Connector Family](#) = ARINC 404
- Dielectric Material = Fluoropolymer

Electrical Characteristics:

- Connector Impedance (Ω) = 50

Body Features:

- Body Style = Straight
- Material = Beryllium Copper
- Ferrule Material = Copper
- Ferrule Plating = Tin
- Shell Material = Brass
- Shell Plating = Gold per MIL-G-45204

Contact Features:

- Contact Type = Pin
- [Contact Plating, Mating Area, Material](#) = Gold (50)
- [Contact Size](#) = 9
- [Contact Configuration](#) = Coax

Industry Standards:

- Government/Industry Qualification = No
- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process

Conditions for Usage:

- [Applies To](#) = Coaxial Cable

Other:

- Brand = AMP

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [AODA Accessibility Policy](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed



