




9-2013522-0 Product Details



9-2013522-0

TE Internal Number: 9-2013522-0

Active

Dynamic Series Connectors

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Dynamic Series Product Line
- D-3900 Series
- Series No. = 3000
- Applies To Printed Circuit Board
- Connector

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) |
 [Request Sample](#) |
 [Find Similar Products](#) |
 [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [DYNAMIC D3900S 7.5mmPITCH REC ASSY \(SPRING CLAMP TYP... \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [DYNAMIC D3900 SPRING CLAMP \(PDF, Japanese\)](#)

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Related Products:

- [Tooling](#)

[List all Documents](#)

Feedback

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Line = Dynamic Series
- Product Type = Connector
- Connector Type = Header
- [PCB Mounting Orientation](#) = Right Angle
- [PCB Mount Retention](#) = With

Electrical Characteristics:

- Operating Voltage Reference = AC
- Operating Voltage (VAC) = 250

Termination Features:

- Termination Method to PC Board = Through Hole

Contact Features:

- Contact Type = Pin
- [Contact Plating, Mating Area, Material](#) = Gold (15)

Housing Features:

- Connector Style = Plug
- [Housing Material](#) = Thermoplastic - GF

Configuration Features:

- [Number of Positions](#) = 7 to 10
- [Number of Rows](#) = 1

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant

Identification Marking:

- [Keying](#) = Z

Conditions for Usage:

- [Applies To](#) = Printed Circuit Board

Packaging Features:

- [Packaging Method](#) = Tube
- [Packaging Quantity](#) = 20

Other:

- Series = D-3900
- Series No. = 3000
- Brand = TE Connectivity

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)

Keep Me Informed



[Supplier Portal](#)

[Product Compliance Support Center](#)

[Manage Your Account](#)



[Careers](#)

[Site Map](#)

[Terms & Conditions](#)

[Privacy Policy](#)

[AODA Accessibility Policy](#)

[AODA Multi-Year Accessibility
Plan](#)