

## EET-0632P-9 Product Details

[Share](#) [Print](#) [Email](#)


**EET-0632P-9**  
(6-1768017-5)

TE Internal Number: 6-1768017-5

 [Active](#)

### Label ID Products

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Printer Type = Thermal Transfer
- Label Height = 6.40 mm
- Label Width = 22.90 mm
- Polyester Material
- EET Series

[View all Features](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

 [Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [EET 0632](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Material](#) = Polyester
- Series = EET
- Energy Label Type = Pressure Sensitive
- [Color](#) = White

#### Electrical Characteristics:

- [Printer Type](#) = Thermal Transfer
- [Number of Labels Across](#) = 2
- Web Width (mm [in]) = 70.00 [2.760]

#### Body Features:

- Recommended Printer = TE3124
- Recommended Ribbon = TTB-110SC/300

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Printer/Label Features:

- [Label Height \(mm \[in\]\)](#) = 6.40 [0.252]
- [Label Width \(mm \[in\]\)](#) = 22.90 [0.900]
- Tamper Evident = No
- [Label Type](#) = Die-Cut
- Adhesive Type = Permanent Acrylic

#### Environmental:

- [Operating Temperature \(°C \[°F\]\)](#) = -40 - +150 [-40 - +302]

#### Conditions for Usage:

- Energy Product = Yes

#### Other:

- Brand = Tyco Electronics
- Comment = Alternative printers and ribbons are available for special applications.

### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

### Customer Support

[Email or Chat With Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage your Account](#)

### Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address 

