




TXR40AB00-2018BI Product Details

[Share](#) | [Print](#) | [Email](#)


Braid, Fixed, Spin and Tinel Lock Adapters

[Not EU RoHS or ELV Compliant](#)

Product Highlights:

- Applies To Cable
- Style = Tinel Lock
- Connector Code = 40
- Straight
- Shell Size = 21, G

[View all Features](#)

TXR40AB00-2018BI

TE Internal Number: 832825-000

 [Active](#)

[Add to My Part List](#)
 [Request Sample](#)
 [Find Similar Products](#)
 [Buy Product](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [Tinel-Lock Adapter](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Style](#) = Tinel Lock
- [Angle](#) = Straight
- [Shell Size](#) = 21, G
- Finish = Cadmium Plating over Electroless Nickel
- Material = Aluminum Alloy
- Color = Olive Drab

Electrical Characteristics:

- [Boot Diameter \(mm \[in\]\)](#) = 36.19 [1.425]
- [Entry Diameter \(mm \[in\]\)](#) = 28.60 [1.130]
- Finish Code = B

Body Features:

- [Connector Code](#) = 40
- [Entry Size](#) = 18
- [Cable Diameter \(Max.\) \(mm \[in\]\)](#) = 28.07 [1.105]

Configuration Features:

- [Braid](#) = Double 36 AWG Braid, Single 30 AWG Braid
- Material Code = A

Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process

Conditions for Usage:

- Applies To = Cable

Other:

- Brand = Raychem

Corporate Information

[Who We Are](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

Quick Links

[Check Distributor Inventory](#)

[Cross Reference](#)

[Find Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Search Knowledge Base](#)

[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

