




TXR40AB90-1605BI Product Details

[Share](#) | [Print](#) | [Email](#)


TXR40AB90-1605BI

TE Internal Number: 227153-000

Active

Braid, Fixed, Spin and Tinel Lock Adapters

[Not EU RoHS or ELV Compliant](#)

Product Highlights:

- Applies To Cable
- Style = Tinel Lock
- Connector Code = 40
- 90°
- Shell Size = 17, E

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)
[Request Sample](#)
[Find Similar Products](#)
[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [Tinel-Lock Adapter](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Style](#) = Tinel Lock
- [Angle](#) = 90°
- [Shell Size](#) = 17, E
- Finish = Cadmium Plating over Electroless Nickel
- Material = Aluminum Alloy
- Color = Olive Drab

Electrical Characteristics:

- [Entry Size](#) = 5
- [Boot Diameter \(mm \[in\]\)](#) = 15.54 [0.612]
- [Entry Diameter \(mm \[in\]\)](#) = 7.92 [0.312]
- Finish Code = B

Body Features:

- [Connector Code](#) = 40
- [Cable Diameter \(Max.\) \(mm \[in\]\)](#) = 7.41 [0.292]

Configuration Features:

- [Braid](#) = Double 36 AWG Braid, Single 30 AWG Braid
- Material Code = A

Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process

Conditions for Usage:

- Applies To = Cable

Other:

- Brand = Raychem

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

