



SLC40AB-1208A Product Details

[Share](#) | [Print](#) | [Email](#)


SLC40AB-1208A

TE Internal Number: CX5693-000

 **Active**

Braid, Fixed, Spin and Tinel Lock Adapters

[Not EU RoHS or ELV Compliant](#)

Product Highlights:

- Applies To Cable
- Style = Raychem Spinlock Variable Angle Backshells
- Connector Code = 40
- 45°, 90°, Straight
- Shell Size = 12

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) |
 [Request Sample](#) |
 [Find Similar Products](#) |
 [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [Spin-Lock Adapter Saddle Clamp, Code 40](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Style](#) = Raychem Spinlock Variable Angle Backshells
- [Angle](#) = 45°, 90°, Straight
- [Shell Size](#) = 12
- Finish = Cadmium over Nickel
- Material = Aluminum

Electrical Characteristics:

- [Entry Diameter \(mm \[in\]\)](#) = 12.70 [0.500]
- Manufacturer = Raychem
- Finish Code = B
- Tinel-Lock Ring Supplied = TR08AI

Body Features:

- [Connector Code](#) = 40
- [Entry Size](#) = 8
- [Cable Diameter \(Max.\) \(mm \[in\]\)](#) = 4.93 - 8.33 [0.190 - 0.328]

Configuration Features:

- Material Code = A

Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process

Conditions for Usage:

- Applies To = Cable

Other:

- Brand = Raychem

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

