




TCFS-16-62C-020-100CH Product Details

 [Share](#)

 [Print](#)

 [Email](#)



TCFS-16-62C-020-100CH

TE Internal Number: 511381-000

 [Active](#)

Heat Shrinkable Cable Kits and Assemblies

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Heat Shrinkable Cable Feedthrough
- Mount Type = Bulkhead Feedthrough
- Thread Size = M16 x 1.5
- Stainless Steel Feedthrough Material
- Electroless Nickel Feedthrough Finish

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [Customer Drawing](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Heat Shrinkable Cable Feedthrough
- [Thread Size](#) = M16 x 1.5
- [Material](#) = Low Fire Hazard Material
- [Angle](#) = Straight

Electrical Characteristics:

- Modification = None
- [Shielded](#) = Yes
- [Expanded ID, Min. \(mm \[in\]\)](#) = 8.50 [0.334]
- [Recovered ID, Max. \(mm \[in\]\)](#) = 6.00 [0.236]

Termination Features:

- [Adhesive](#) = S-1030 Holt Melt

Body Features:

- Mount Type = Bulkhead Feedthrough
- Feedthrough Material = Stainless Steel
- Feedthrough Finish = Electroless Nickel
- [Feedthrough Type](#) = Single-sided
- Thread Length (mm [in]) = 20.00 [0.787]
- [Feedthrough Inner Diameter, Max. \(mm \[in\]\)](#) = 10.2 [0.4]
- A/F Body Diameter (mm [in]) = 29 [1.14]
- A/F Nut (mm [in]) = 22 [0.87]
- Length of Molded Part/Flange (mm [in]) = 65 [2.559]
- Hole Diameter (mm [in]) = 17.00 [0.669]

Configuration Features:

- [Material Code](#) = 100

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- Brand = Raychem

Corporate Information

[Who We Are](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

Quick Links

[Check Distributor Inventory](#)

[Cross Reference](#)

[Find Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Search Knowledge Base](#)

[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

