



Connectors > D-Shaped Connectors > D-Sub Accessories > Locking & Mounting



D-Shaped Connector Accessories: **Female Screwlock Assembly Kit**

Screw Length: **11.94 mm [.47 in]**

Features

Product Type Features

Product Type	Accessory
D-Shaped Connector Accessories	Female Screwlock Assembly Kit

Mechanical Attachment

Screwlock Style	Screwlock with Lockwasher and Hex Nut
Screw Finish	Yellow Chromate
Screw & Hole Thread Size	4-40 UNC
Screw Length	11.94 mm[.47 in]

Dimensions

Thread Length	7.23 mm[.285 in]
---------------	------------------

Packaging Features

Packaging Quantity	1
Packaging Method	Bag, Kit

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5748271-4
FEMALE SCREWLOCK KIT

Also in the Series | AMPLIMITE Kit

 D-Sub Backshells & Clamps(135)	 D-Sub Contact Accessories(1)	 D-Sub Covers(3)	 D-Sub Locking & Mounting(122)
---	--	--	--



Documents

Product Drawings
FEMALE SCREWLOCK KIT

English

CAD Files
3D PDF

3D

Customer View Model
ENG_CVM_CVM_5748271-1_A.2d_dxf.zip

English

Customer View Model
ENG_CVM_CVM_5748271-1_A.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_5748271-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance
TE Material Declaration

English

Instruction Sheets
Instruction Sheet (U.S.)

English