

KLN1250A1/4

✓ ACTIVE

Alcoswitch | Alcoswitch KLN

TE Internal #: 9-1437621-4

Switch Knobs, Knob, Aluminum, Straight Knurl Knob Design, 6.35 mm [.25 in] Shaft Size, 31.75 mm [1.25 in] Diameter, Natural, Line, Alcoswitch KLN

[View on TE.com >](#)



Relays, Contactors & Switches > Switches > Switch Knobs



Switch Knob Product Type: **Knob**
Switch Knob Material: **Aluminum**
Knob Design: **Straight Knurl**
Shaft Size: **6.35 mm [.25 in]**
Switch Knob Diameter: **31.75 mm [1.25 in]**

Features

Product Type Features

Switch Knob Product Type	Knob
--------------------------	------

Configuration Features

Skirt	Without
Spinner	Without
Spin Plate	Without
Knob Design	Straight Knurl


Body Features

Switch Knob Material	Aluminum
Switch Knob Color	Natural

Dimensions

Shaft Size	6.35 mm[.25 in]
Switch Knob Diameter	31.75 mm[1.25 in]

Identification Marking





Indicator Style	Line
Indicator Location	Top & Side

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 9-1437621-5
KLN1250B1/4=KNOB KNURL W/IND L



TE Part # 9-1437621-9
KLN500B1/8=KNOB KNURL W/IND LI




TE Part # 9-1437621-8
KLN500B1/4=KNOB KNURL W/IND LI



TE Part # 9-1437621-7
KLN500A1/8=KNOB KNURL W/IND LI

Also in the Series | Alcoswitch KLN



Documents

Product Drawings

KLN1250A1/4=KNOB KNURL W/IND L

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_9-1437621-4_99_c-9-1437621-4-99.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_9-1437621-4_99_c-9-1437621-4-99.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_9-1437621-4_99_c-9-1437621-4-99.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Alcoswitch Products

English