

Item Number **7224800**

Widespan Ceiling Fan

100 in. Matte Black Finish
Black Blades

Specifications

Size	100"
Blades.....	Aluminum Blades (Black)
Blade Pitch.....	17°
Approved Location	Indoor
Suggested Room Size.....	High Ceiling (Greater than 10')
Down Rod.....	3/4" x 24"
Installation.....	Down Rod Only
Max. Ceiling Angle.....	N/A
Lead Wire	30"
Light Bulb Usage.....	N/A
Control	Remote Control Included
Motor Finish.....	Matte Black
Motor Material	DC Motor 165mm x 30mm
Reverse Airflow.....	Yes
Capacitor	N/A
Switch Housing Cap.....	Not Included



Energy Information

	With down rod	Hugger/ Without down rod
Airflow (CFM) when operated at high speed.....	19094	N/A
Energy Use (excludes lights) ^Δ	N/A	N/A
Airflow (CFM) ^Δ	N/A	N/A
Airflow Efficiency (CFM/W) ^Δ	254	N/A
Estimated Yearly Energy Cost ^Δ	N/A	N/A
RPM (High)	75	
Amp (High)	1.55	
Watts (High)	116	



Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

®, WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation.
Used under license by Westinghouse Lighting. All Rights Reserved.

^Δ Based on typical use, excluding lights

* Based on 12 cents per kWh and 6.4 hours use per day


2020

Item Number **7224800**

Widespan Ceiling Fan

100 in. Matte Black Finish
Black Blades

A. Top of Canopy to Bottom of Blades	33"
B. Top of Canopy to Bottom of Switch House	N/A
C. Top of Canopy to Bottom of Canopy	3"
D. Width of Motor Housing.....	11.8"
E. Width of Canopy.....	7.5"
F. Top of Canopy to Bottom of Glass	N/A



If a Combo Style Fan with a 4" Down Rod is installed without the Down Rod, Subtract 3" from the Dimensions Listed (A, B, F).
If a Combo Style Fan with a 6" Down Rod is installed without the Down Rod, Subtract 5" from the Dimensions Listed (A, B, F).

Warranty

Ceiling fans backed by our 15-year Limited Warranty have a 15-year motor warranty and a 2-year warranty on all other parts.

Caution

This ceiling fan has thin blades and operates at higher speeds than traditional ceiling fans. Severe injury can result if any part of the body comes in contact with these fast-moving blades. For safe operation, this product must be installed with a minimum clearance of 10 feet from the floor to the lowest edge of the fan blades.

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

, WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation.
Used under license by Westinghouse Lighting. All Rights Reserved.