



LUMAWISE | LUMAWISE LED Holders

TE Internal #: 5-2154874-2

LED Holders, Cree CXA 15xx, Enables Zhaga Compatibility / Not Optic Compatible, 250 VDC, Poke-In, Wire-to-Component, 2 Position, LUMAWISE LED Holders

[View on TE.com >](#)

Connectors > Lighting Connectors > LED Holders



Compatible LED: **Cree CXA 15xx**

Lighting Connector Features Included: **Enables Zhaga Compatibility, Not Optic Compatible**

Operating Voltage: **250 VDC**

Termination Method to Wire & Cable: **Poke-In**

Connector System: **Wire-to-Component**

Features

Product Type Features

Product Type	LED Holder
Connector System	Wire-to-Component
Sealable	No

Configuration Features

Lighting Connector Features Included	Enables Zhaga Compatibility, Not Optic Compatible
--------------------------------------	---

Number of Positions	2
---------------------	---

Electrical Characteristics

Current Rating (Max)	3 A
----------------------	-----

Operating Voltage	250 VDC
-------------------	---------

Body Features

Compatible LED	Cree CXA 15xx
----------------	---------------

Contact Features

Contact Mating Area Plating Material	Gold
--------------------------------------	------



Contact Base Material	Copper Alloy
-----------------------	--------------

Contact Current Rating (Max)	3 A
------------------------------	-----

Termination Features

Termination Method to Wire & Cable	Poke-In
------------------------------------	---------

Housing Features

Housing Material	PBT GF
------------------	--------

Usage Conditions

Operating Temperature Range	-40 – 105 °C
-----------------------------	--------------

Operation/Application

Circuit Application	Power
---------------------	-------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
--	---

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not applicable for solder process capability
---------------------------	--


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | LUMAWISE LED Holders



Documents

Product Drawings

[LED Holder for Cree CXA15XX \(1pc\)](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_5-2154874-2_A_c-5-2154874-2-a.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5-2154874-2_A_c-5-2154874-2-a.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5-2154874-2_A_c-5-2154874-2-a.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1-1773700-4_LED HOLDER TYPE CREE](#)

English

[1-1773706-3_SCALABLEOVERVIEW_BROCHURE](#)

English



[8-1773700-9_LEDBROCHURE](#)

English

[8-1773700-9_LEDBROCHURE](#)

Japanese

[Product Specifications](#)

[Application Specification](#)

English

[Agency Approvals](#)

[UL Report](#)

English