

SeeSnake® CS10 Monitor

Digital Recording Monitor

NEW

The RIDGID® SeeSnake® CS10 Monitor combines RIDGID durability with the easiest to use Digital Recording Monitor in the industry. One touch recording allows you to record snapshots and video to a USB Thumbdrive, and then hand it directly to your customer.

- **USB Thumb Drive Recording** lets you record digitally into a format that your customer can read on their computer.
- **12.1" Daylight Readable Display** allows you to easily monitor and record inspections in bright outdoor environments.
- **Multi Mode Recording** lets you take snapshots, record full frame video and record in a lean video format called Auto-log (small files).
- **Software Integrations** with SeeSnake HQ and RIDGIDConnect.com allow you to deliver your inspections in a wide array of formats from online to DVD.

Specifications

Weight 12.2 lbs./5,5 kg
 Length 14.3"/36,3 cm
 Width 11.9"/30,2 cm
 Height 12.4"/31,5 cm
 Display 12.1" Daylight Readable LCD
 Resolution 640 x 480
 Power Source 1 or 2 RIDGID 18V Batteries or AC Plug
 Audio Integrated Microphone and Speaker
 Video AVI 30FPS - 720 x 480 NTSC
 Image JPG - 720 x 480
 Transfer USB Thumb Drive




Ordering Information

Catalog No.	Description	Weight		Std Pack
		(lbs.)	kg	
39328	CS-10 Digital Monitor	12.2	5,5	1
39338	CS-10 Monitor w/ 2 Batteries and Charger	15.8	7,17	1

SeeSnake® HQ Installed PC Software (Included)

Report on and Deliver inspection results with this powerful software package. Simply import your inspections from your CS10 into SeeSnake HQ via USB thumb drive.

- Edit Video and Images
- Burn Digital to DVD
- Fill out detailed job reports
- Publish, Edit and Share your Reports via RIDGIDConnect.com



SeeSnake HQ Screenshot

RIDGIDConnect The Ultimate Digital Upgrade

Share, Store and Simplify with the RIDGIDConnect Inspection hosting system.

- 24/7 access anywhere to your videos and jobs
- Collaborate with Employees and Partners
- Stay in Contact with your Customers
- Protect and Maintain your Valuable Data
- Send Professional Interactive Reports to one or many recipients instantly



www.RIDGIDConnect.com Screenshot

Recommended Reels


Catalog No.	Description	Weight		Std Pack
		lbs.	kg	
14053	200' Color Reel	53	24,1	1
14058	325' Color Reel	62	28,2	1
13988	200' Self-Leveling Color Reel	52	24,1	1
13998	325' Self-Leveling Color Reel	62	28,2	1
14063	200' Mini Color Reel	29	13,2	1
35183	100' microReel L100C w/Counter	10.3	4,7	1



Mini SeeSnake® Plus



SeeSnake® microReel



Standard SeeSnake® Plus (Self Leveling/Color)

Distributor

For the complete selection of the RIDGID product line, please refer to the Ridge Tool Catalog or www.RIDGID.com.