

ALBION®

CASTERS AND WHEELS

Heavy Duty Casters Small Plate

- Double Row Swivel Raceways
- Heat Treated and Factory Lubricated Raceways
- Yellow Zinc Chromate Finish

Applications: Platform Trucks, Warehouse Trucks, Material Handling Containers, Dollies, Waste Disposal Trucks, Floor Trucks, Shop Carts



930MD05201SL




930XA05201SB



930TM05201ST



930CA05201R



Overall Size: 4" x 4-1/2"
Hole Spacing: 2-5/8" x 3-5/8"
 slotted to 3" x 3"
Bolt Dia.: 3/8"

Wheel Dia. (In.)	Tread Width (In.)	Load Rating (lbs.)	Overall Height (In.)	Swivel Part Number	Swivel W/Brake Part Number	Total-Lock Part Number	Directional-Lock Part Number	Rigid Part Number
Soft Rubber Tread on Aluminum Core Wheel (Roller Bearing)								
5	2	350	6-1/2	930MD05201S	930MD05201SB	930MD05201ST	930MD05201SL	930MD05201R
6	2	410	7-1/2	930MD06201S	930MD06201SB	930MD06201ST	930MD06201SL	930MD06201R
8	2	500	9-1/2	930MD08201S	930MD08201SB	930MD08201ST	930MD08201SL	930MD08201R
Polyurethane Tread on Polyolefin Core Wheel (Roller Bearing)								
4	2	600	5-5/8	930XA04201S	930XA04201SB	NA	NA	930XA04201R
5	2	750	6-1/2	930XA05201S	930XA05201SB	NA	NA	930XA05201R
6	2	900	7-1/2	930XA06201S	930XA06201SB	NA	NA	930XA06201R
8	2	900	9-1/2	930XA08201S	930XA08201SB	NA	NA	930XA08201R
Polyurethane Tread on Aluminum Core Wheel (Roller Bearing)								
4	2	750	5-5/8	930PD04201S	930PD04201SB	NA	NA	930PD04201R
5	2	1050	6-1/2	930PD05201S	930PD05201SB	930PD05201ST	930PD05201SL	930PD05201R
6	2	1200	7-1/2	930PD06201S	930PD06201SB	930PD06201ST	930PD06201SL	930PD06201R
8	2	1200	9-1/2	930PD08201S	930PD08201SB	930PD08201ST	930PD08201SL	930PD08201R
Phenolic Wheel (Roller Bearing)								
3-1/4	2	700	5-1/4	930TM03201S	NA	NA	NA	930TM03201R
4	2	800	5-5/8	930TM04201S	930TM04201SB	NA	NA	930TM04201R
5	2	1000	6-1/2	930TM05201S	930TM05201SB	930TM05201ST	930TM05201SL	930TM05201R
6	2	1200	7-1/2	930TM06201S	930TM06201SB	930TM06201ST	930TM06201SL	930TM06201R
8	2	1200	9-1/2	930TM08201S	930TM08201SB	930TM08201ST	930TM08201SL	930TM08201R
Semi-Steel Wheel (Roller Bearing)								
4	2	1000	5-5/8	930CA04201S	930CA04201SB	NA	NA	930CA04201R
5	2	1000	6-1/2	930CA05201S	930CA05201SB	NA	NA	930CA05201R
6	2	1200	7-1/2	930CA06201S	930CA06201SB	NA	NA	930CA06201R
8	2	1200	9-1/2	930CA08201S	930CA08201SB	NA	NA	930CA08201R
Polyurethane Tread on Polyolefin Core Wheel (Delrin Bearing) NSF Certified								
5	2	750	6-1/2	930XA05252SN	NA	930XA05252STN	NA	930XA05252RN
6	2	900	7-1/2	930XA06252SN	NA	930XA06252STN	NA	930XA06252RN
8	2	900	9-1/2	930XA08252SN	NA	930XA08252STN	NA	930XA08252RN

