

GasAlertClip EXTREME

Single-Gas Detector

H₂S, CO, O₂, SO₂





Up to three years of continuous maintenance-free protection

Simply press the start/test button and the GasAlertClip Extreme is ready to use, providing continuous, reliable protection. Available in two year (H₂S, CO, O₂, SO₂) or three year (H₂S, CO) versions, this single gas detector requires no calibration, sensor replacement, battery replacement or battery charging. Compatible with the MicroDock II automatic test system, the simplicity of the GasAlertClip Extreme combined with minimal training requirements and negligible maintenance costs make the GasAlertClip Extreme one of the most cost-effective gas detection solutions for facility workers and onsite contractors.

Standard Package Contents

- Detector complete with specified sensor, stainless steel alligator clip and concussion-proof housing
- Test cap
- Instructions

General Specifications

Size	1.1 x 2.0 x 3.2 in. / 2.8 x 5.0 x 8.1 cm
Weight	2.7 oz. / 76 g
Typical battery life	Two years (H ₂ S, CO, SO ₂ or O ₂) or three years (H ₂ S or CO)
Certifications and approvals	<p>  Class I, Div. 1, Gr. A, B, C, D  American Bureau of Shipping ATEX: CE II 1 G T4 Ex ia IIC T4 IECEX: Ex ia IIC T4 CE: European Conformity </p>
Warranty	Two or three years from activation (given normal operation), plus one year shelf life

5472-14

GasAlertClip Extreme (continued)

GasAlertClip Extreme 2-Year Detectors

	Alarm Setpoint	Order Number*
Hydrogen sulfide (H ₂ S)	Low - 10 ppm / High - 15 ppm	GA24XT-H
Hydrogen sulfide (H ₂ S) - bulk pack	Low - 10 ppm / High - 15 ppm	GA24XT-H-B50
Hydrogen sulfide (H ₂ S)	Toggle between 5/10 and 10/15	GA24XT-H510
Carbon monoxide (CO)	Low - 35 ppm / High - 200 ppm	GA24XT-M
Carbon monoxide (CO)	Low - 30 ppm / High - 200 ppm	GA24XT-M30200
Carbon monoxide (CO)	Low - 50 ppm / High - 200 ppm	GA24XT-M50200
Sulfur dioxide (SO ₂)	Low - 5 ppm / High - 10 ppm	GA24XT-S
Oxygen (O ₂)	Low - 19.5% / High - 23.5%	GA24XT-X
Oxygen (O ₂)	Low - 19.5% / High - 22.5%	GA24XT-X19.522.5
To order a 50-unit bulk package (one model type per pack only)		Add Suffix "-B50"

GasAlertClip Extreme 3-Year Detectors

	Alarm Setpoint	Order Number*
Hydrogen sulfide (H ₂ S)	Low - 10 ppm / High - 15 ppm	GA36XT-H
Hydrogen sulfide (H ₂ S)	Low - 5 ppm / High - 10 ppm	GA36XT-H510
Carbon monoxide (CO)	Low - 35 ppm / High - 200 ppm	GA36XT-M
Carbon monoxide (CO)	Low - 30 ppm / High - 200 ppm	GA36XT-M30200
Carbon monoxide (CO)	Low - 50 ppm / High - 200 ppm	GA36XT-M50200
To order a 50-unit bulk package (one model type per pack only)		Add Suffix "-B50"

* Add "-BR" to the end of the order number for INMETRO certified detectors (for Brazil only).



Bulk Package

Bulk packaging is the environmentally friendly choice for easy distribution and space efficiency. (Add suffix "-B50" for 50-unit bulk package.)

GasAlertClip Extreme (continued)

Carrying Accessories	Order Number
Concussion-proof boot with stainless steel alligator-style clip	GA24-BALERT
Splash guard filters, kit of 5 for use with concussion-proof boot (GA24-BALERT)	GA-BSPLASH-K
Belt clip with screw	GA-CL-1
Hard hat clip (non-conductive)	GA-HC-1
Alligator-style clip (non-conductive)	GA-AG-1
Alligator-style clip (stainless steel - included with detector)	GA-AG-2
Neck strap with safety release	GA-NS-1
Short strap (6 in. / 15.2 cm)	GA-LY-1
Extension strap (4 ft. / 1.2 m)	GA-ES-1

Event Logging Accessories	Order Number
IR DataLink USB adaptor	GA-USB2

Testing Equipment and Spares	Order Number
Test cap and hose (1 ft. / 0.3 m)	GA-TC-1
MicroDock II Automated Calibration and Testing Station with GasAlertClip Extreme module:	
- H ₂ S (hydrogen sulfide)	DOCK2-2-1E-00-G
- SO ₂ (sulfur dioxide)	DOCK2-2-1F-00-G
- CO (carbon monoxide)	DOCK2-2-1G-00-G
- O ₂ (oxygen)	DOCK2-2-1H-00-G
GasAlertClip Extreme MicroDock II docking module:	
- H ₂ S (hydrogen sulfide)	DOCK2-0-1E-00-G
- SO ₂ (sulfur dioxide)	DOCK2-0-1F-00-G
- CO (carbon monoxide)	DOCK2-0-1G-00-G
- O ₂ (oxygen)	DOCK2-0-1H-00-G

For complete MicroDock II system configuration information, see MicroDock II section.

Calibration & Testing Equipment
 For calibration and testing equipment for this product, please see pages 82-85.



MicroDock II
 Automatic test and calibration station (see MicroDock II section for additional information)



Hard Hat Clip
 GA-HC-1



Splash Guard Filters
 GA-BSPLASH-K
 For concussion-proof boot



Concussion-Proof Boot
 GA24-BALERT



IR DataLink
 GA-USB2
 USB adaptor