



GREENLEE[®]
A Textron Company

There With You[™]
faster • safer • easier[®]

TK-30GFI

GFCI Electrical Kit

Three of Greenlee's
electrician products
in a versatile kit



A multi-purpose kit for everyday electrical needs

Greenlee is proud to introduce to its product line the GFCI Electrical Kit. The TK-30GFI Electrical Kit includes three of Greenlee's basic electrician products: the DM-20 manual ranging multimeter, the GT-11 non-contact voltage detector, and the GT-10GFI circuit tester. Recommended as standard fare for an electrician's tool bag, these items come with a durable carrying case for easy storage and portability.

The TK-30GFI Electrical Kit meets the latest industry safety standards and is backed by a lifetime limited warranty. For further information on this product as well as other Greenlee products, please visit www.greenlee.com.

Features

DM-20

- Measure voltage and check batteries.
- Great for measuring current of small electronic circuits.
- Includes rubber boot to protect meter from damage.
- AC/DC voltage, DC amperage measurement.
- Built-in test leads, no loose parts to lose.
- Resistance measurement.
- Audible continuity and diode tests.
- Tests 1.5 V and 9 V batteries.
- Lifetime Limited Warranty.

Contents/Accessories-

- Protective Boot, (1) 9V Battery

Specifications

DM-20

Voltage measurement:

AC V: 200.0, 300 DC V: 200.0 m; 2.000, 20.00, 200.0, 300

Amperage measurement:

DC A: 2000 m; 20.00, 200.0 m

Resistance measurement:

200.0, 2000 Ω; 20.00, 200.0, 2000 kΩ

Measurement category:

CAT II, 300 V

GT-11

- Use to detect voltage in outlets, lighting fixtures, circuit breakers, wires and cables or to find a break in a wire.
- Safe, non-contact voltage detection.
- Bright LED and audible alarm sound if voltage is present.
- On/Off switch for longer battery life.
- Convenient pen-size device easily fits into pockets or tool pouches.
- Lifetime Limited Warranty.

Contents/Accessories-

- (2) 1.5 V AAA batteries

GT-11

Voltage Detection:

50V -1000V AC

Frequency:

50-500 Hz

Measurement category:

CAT IV, 1000V

GT-10GFI

- Use to trouble shoot 120V AC grounded outlets and test GFCI receptacles.
- Light sequence indicates correct / incorrect wiring.
- Lifetime Limited Warranty.



DM-20 Digital Multimeter



GT-11 Non-Contact Voltage Detector



GT-10GFI Circuit Tester

Ordering Information

CAT.	UPC	DESCRIPTION	QTY
TK-30GFI	10268	Electrical Kit, GFCI	1

DISTRIBUTOR INFORMATION :

USA Tel: 800.435.0786
Fax: 800.451.2632

Canada Tel: 800.435.0786
Fax: 800.524.2853

International Tel: +1.815.397.7070
Fax: +1.815.397.9247