

## Item Number 7802400

## Contractor Choice Ceiling Fan

52 in. White Finish  
White Blades



### Specifications

Size .....	52"
Blades.....	MDF Blades (White)
Blade Pitch.....	12°
Approved Location .....	Indoor
Suggested Room Size.....	Large Room (up to 15x15)
Down Rod.....	3/4" x 4"
Installation.....	Combo
Max. Ceiling Angle.....	11°
Lead Wire .....	78"
Light Bulb Usage.....	N/A
Control.....	Remote Control Adaptable
Motor Finish.....	White
Motor Material .....	Silicon Steel Motor 153mm x 15mm
Reverse Airflow.....	Yes
Capacitor .....	Triple
Switch Housing Cap.....	Not Included

### Energy Information

	<u>With down rod</u>	<u>Hugger/ Without down rod</u>
Airflow (CFM) when operated at high speed.....	4271	4099
Energy Use (excludes lights) <sup>Δ</sup> .....	39	39
Airflow (CFM) <sup>Δ</sup> .....	2981	2893
Airflow Efficiency (CFM/W) <sup>Δ</sup> .....	77	75
Estimated Yearly Energy Cost <sup>Δ</sup> .....	\$11	\$11
RPM (High) .....	175	
Amp (High).....	0.54	
Watts (High).....	65	



Specifications are subject to change without notice, please visit [www.westinghouselighting.com](http://www.westinghouselighting.com) for latest information.

®, WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation.  
Used under license by Westinghouse Lighting. All Rights Reserved.

## Item Number 7802400

## Contractor Choice Ceiling Fan

52 in. White Finish  
White Blades

A. Top of Canopy to Bottom of Blades .....	10.3"
B. Top of Canopy to Bottom of Switch House .....	11.3"
C. Top of Canopy to Bottom of Canopy .....	2.3"
D. Width of Motor Housing.....	9"
E. Width of Canopy.....	5.3"
F. Top of Canopy to Bottom of Glass.....	N/A




If a Combo Style Fan with a 4" Down Rod is installed without the Down Rod, Subtract 3" from the Dimensions Listed (A, B, F).  
If a Combo Style Fan with a 6" Down Rod is installed without the Down Rod, Subtract 5" from the Dimensions Listed (A, B, F).

## Warranty

Ceiling fans backed by our Limited Lifetime Warranty have a lifetime motor warranty and a 2-year warranty on all other parts.

Specifications are subject to change without notice, please visit [www.westinghouselighting.com](http://www.westinghouselighting.com) for latest information.

 WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation.  
Used under license by Westinghouse Lighting. All Rights Reserved.