



Product Conversion Series

CRC® Knock'er Loose®



Issue: Rust & corrosion lead to seized, bound and frozen fasteners, which affect the smooth operation and repair of plant machinery, leading to unnecessary downtime and lost revenue.

Application: Whether performing routine maintenance or emergency repairs, quick disassembly of machinery, tools and equipment is key to operating efficiency and improved performance. For the quick removal of nuts & bolts, pins, screws, bushings, clips, hinges, snaps, lugs, caps, locks, washers and sliding mechanisms, you need a fast & effective penetrant.

Recommendation: Use CRC® Knock'er Loose® Penetrating Solvent which is an industrial strength, low viscosity lubricant and penetrant designed to quickly loosen and free seized, bound and frozen fasteners. It quickly permeates rust, scale, gum, grease and corrosion with a low surface tension formula that creeps into cracks, seams, threads and joints with greater efficacy than the competition.



Product Features & Benefits:

Industrial Strength Formula

- Specially formulated to dissolve rust, gum & varnish
- Lubricating residue prevents corrosion from returning
- Outperforms competition as verified by laboratory testing

MSD[L]™

- Material Safety Data Sheet printed on reverse side of aerosol label
- Instant source of disposal and first aid information

NSF Registered

- NSF H2 Registered for use in meat & poultry plants
- NSF Registration No. 132079

VOC Compliant Nationwide

- Complies with current state & federal VOC regulations

Convenient 360° Spray Valve

- 360° spray valve can be sprayed from any position



Available Sizes:

- 03016 - 6 oz. aerosol
- 03020 - 16 oz. aerosol
- 03021 - 1 gallon bottle
- 03022 - 5 gallon pail
- 03023 - 55 gallon drum
- 03024 - 16 oz. non-aerosol
- 03025 - 8 oz. spout can
- 03031 - 24 oz. aerosol




See Reverse for Kroil® Conversion Details

Knock'er Loose® vs. Kano® Kroil®

Why replace Kano® Kroil®?



- 1 Performance** - As shown in the laboratory tests below, Knock'er Loose® outperforms Kroil® in penetration & spreadability. Knock'er Loose® will penetrate farther into minute cracks and crevices more rapidly than Kroil®.



- 2 NSF Registration** - Kroil® is not NSF registered for use in meat & poultry plants and is not considered a food grade lubricant.



- 3 VOC Compliance** - Kroil® is sold to all purchasers with the Not For Retail Sale statement on their product, which is typically used on non-VOC compliant product.

- 4 CRC Product Offering** - CRC has direct cross replacement products that meet or exceed user expectations on performance, price & compliance.



KROIL	KNOCK'ER LOOSE
8 oz. spout can.....	CRC 8 oz. spout can - #03025
N/A.....	CRC NEW! 6 oz. aerosol - #03016
12 oz. aerosol.....	CRC 16 oz. aerosol - #03020
16 oz. 'king size' aerosol.....	CRC 16 oz. aerosol - #03020
N/A.....	CRC 16 oz. non-aerosol - #03024
20 oz. 'industrial size' aerosol.....	CRC NEW! 24 oz. aerosol - #03031
N/A.....	CRC NEW! 24 oz. aerosol - #03031
1 gallon.....	CRC 1 gallon bottle - #03021
5 gallon.....	CRC 5 gallon pail - #03022
15 gallon.....	CRC 55 gallon drum - #03023
55 gallon.....	CRC 55 gallon drum - #03023



CRC Industries • Warminster, PA 18974
 Customer Service: (800) 272-4620
 MSDS Faxback System: (215) 442-6260
 Technical Assistance: (800) 521-3168
 www.crcindustries.com/ei

Available from: