

Akro-Tubs & Cross-Stack Akro-Tubs

90° Nest & Stack Tub!

- FDA-sanctioned materials; ideal for food processing and industrial operations
- Nests when empty to conserve space. Easy to clean and sanitize



34240



34305 with
34005 lid

34301

34302

34305

34240

Akro-Tub	Dimensions (In.)					Capacity/Qty.			
	Model No.	L	W	H	A	B	Cu. Ft.	Gal.	Lbs.
34240	19	24½	9½	20½	15½	1.95	14.6	75	6

Order in carton quantities.

Cross-Stack Akro-Tub	Outside Dimensions (In.)					Accessories	Capacity/Qty.		
	Model No.	L	W	H	A		B	Lid	Cu. Ft.
34301	17¼	11	8	13¼	7¾	–	0.52	3.85	6
34302	17¼	11	12	12¾	7	–	0.74	5.51	6
34303	23¾	17¼	8	19¾	14	–	1.31	9.81	6
34304	23¾	17¼	12	19	13¼	–	1.92	14.38	6
34305*	25	16	8½	20¾	11½	34005*	1.25	9.75	6


One color per carton. *Specify Blue, Gray or Natural. Order in carton quantities.

Akro-Tubs

- Rounded corner design adds strength
- Rolled top rim forms comfortable handles
- Ribs prevent jamming when nested
- 75-lb. weight capacity per tub

Cross-Stack Akro-Tubs

- Stacking grooves allow stable 90-degree stacks of tubs
- Molded-in handles for comfortable lifting
- Extra-thick walls for superior strength
- Compatible with standard 36" shelving and conveyor systems



Akro-Tub & Cross-Stack Akro-Tub Racks



Double-Sided Cross-Stack Tub Rack

RACR5MR

- Holds (32) 34301 or (16) 34303 Cross-Stack Akro-Tubs (sold separately). Casters: 5" x 2" Mold-On Rubber: 2 Rigid, 2 Swivel



Akro-Tub Rack

RA6TR4MR

- Holds (6) 34240 Akro-Tubs (sold separately). Welded steel frame with 12-gauge base and bolted-on casters. Casters: 4" x 2" Mold-On Rubber: 2 Rigid, 2 Swivel

Racks		Outside Dimensions (In.)			Capacity
Model No.	Description	L	W	H	Lbs.
RA6TR4MR	Akro-Tub Rack	24	24	73	600
RACR5MR	Double-Sided Cross-Stack Akro-Tub Rack	53	29	62	1000



akro-mils.com

1293 South Main Street, Akron, Ohio 44301 • Tel: 800.253.2467 • Fax: 330.761.6348 • sales@akro-mils.com
 In Canada: Ak-West, Inc. • Tel: 877.979.8940 • Fax: 403.225.1696 • sales@ak-westinc.com • ak-westinc.com