

The **Next Small Thing** in **Fast Labeling**



ACTUAL SIZE

It Pays to Think Small

The new Brady MiniMark™ Industrial Label Printer offers an affordable sign and label making solution that is compact, fast, and incredibly versatile.

Brady's MiniMark printer is ideal for:

- Signs
- Pipe Markers
- Equipment ID
- General ID
- Racks and Shelving
- Panel ID
- Procedures
- Asset Management
- And much, much more

Big Benefits in a Small Package

- VERSATILE – Uses continuous tapes for multiple applications
- EASY – Supplies are easy to load
- FAST – Prints up to three inches per second
- COMPACT – Doesn't take up a lot of space in work areas
- Available with parallel, serial, and USB connectivity
- Built-in cutter minimizes waste



MarkWare™ Facility Identification software delivers big advantages

Creating your signs and labels is fast and easy with MarkWare software, a powerful tool to complement your use of the MiniMark printer. Use your PC to quickly design professional-looking signs and labels, and print directly to a Brady labeling system or most Windows® inkjet and/or laser printers.



- Preformatted templates provided for quick and easy label creation.
- Create pipe markers in seconds with the special pipe marker text and graphics.
- Use any font on your PC.
- Choose from over 1,000 safety symbols and industrial pictograms.
- Import logos, photos, and other graphics in a variety of different file formats.
- Create bar codes using 15 different symbologies.
- Customize label layouts to your own specifications with the complete drawing tool kit.



For fast, versatile labeling, think small. Think Brady MiniMark.

For **more information**, or to order your MiniMark Industrial Label Printer, call **1-888-311-0775** or visit **www.bradyid.com/minimark**.

MINIMARK™
INDUSTRIAL LABEL PRINTER

MiniMark Printer, Packages, and Accessories

| Description | Catalog No. |
|--|---------------|
| MiniMark™ Industrial Label Printer | 52041 |
| ValuePLUS Package for MiniMark™ Includes: 1 roll each 4" and 2.25" white vinyl tape; MarkWare™ software; and 1 roll of black ribbon. | 52159 |
| MiniMark™ Industrial Label Printer and HandiMark® Portable Label Maker Combination Kit | 105030 |
| General Industrial Supply Starter Package Includes: MarkWare™ software; 2 rolls each of 4" white and yellow vinyl; 2 rolls each of 2.25" white and yellow vinyl; 2 rolls each of 1.125" white and yellow vinyl; and 8 rolls of black ribbon (4 pkgs.) | 105089 |
| Pipe Marker Supply Starter Package Includes: MarkWare™ software; 3 rolls of 4" yellow vinyl; 1 roll each of 4" red, green, and blue vinyl; 3 rolls of 2.25" yellow vinyl; 1 roll each of 2.25" red, green, and blue vinyl; 1 roll each of 1.125" yellow, red, green, and blue vinyl; and 6 rolls each of black and white ribbon (3 pkgs. each) | 105088 |



Indoor/Outdoor Vinyl Tape Tape Cartridges, 1 per pkg.

| Description | Catalog No. | | |
|-------------|-------------|--------------|---------------|
| | 4" x 110' | 2.25" x 110' | 1.125" x 110' |
| Clear | 52086 | 52073 | 52060 |
| White | 52087 | 52074 | 52062 |
| Yellow | 52090 | 52075 | 52063 |
| Red | 52091 | 52076 | 52064 |
| Green | 52093 | 52077 | 52065 |
| Blue | 52094 | 52078 | 52066 |
| Orange | 52096 | 52079 | 52067 |
| Black | 52143 | 52080 | 52068 |
| Grey | 52144 | 52081 | 52069 |
| Gold | 52145 | 52082 | 52070 |
| Brown | 52146 | 52083 | 52071 |
| Purple | 52147 | 52084 | 52072 |



B427 Self-Laminating Die Cut Labels*

| Description | Catalog No. | Labels/Roll |
|-------------------|-------------|-------------|
| White .5"x 1.25" | 52153 | 2,800/roll |
| 1"x 1" | 52155 | 3,275/roll |
| 1"x 1.25" | 52156 | 2,780/roll |
| 1"x 2.5" | 52157 | 1,485/roll |
| 1.5"x 2.5" | 52158 | 1,000/roll |

*Use Brady black wax ribbon with die cut labels. Part No. 105031

B438 Tamper-Evident Metallized Polyester Labels*

| Description | Catalog No. | Labels/Roll |
|----------------|-------------|-------------|
| Silver 2"x 1" | 52148 | 1,240/roll |
| 3"x 1" | 52149 | 1,225/roll |
| 3"x 2" | 52150 | 650/roll |
| 3"x 110' | 52152 | Continuous |

*Use Brady black wax ribbon with die cut labels. Part No. 105031

Ribbon 4.4" x 290' per roll, 2 rolls/pkg.

| Description | Catalog No. |
|-------------|-------------|
| Black | 52042 |
| White | 52044 |
| Red | 52045 |
| Blue | 52047 |
| Green | 52059 |
| Black Wax | 105031 |



MiniMark™ Printer Specifications

Maximum Printing Width: 4 inches
Minimum Printing Length: From 1 inch to 39 inches

Dimensions: 8 inches wide x 10.25 inches deep
x 7 inches high

Weight: 4.85 pounds

Current – Input: 100-240V / 50 / 60Hz / 1.6A

Current – Output: 24VDC – 2.5A

MiniMARK™
INDUSTRIAL LABEL PRINTER

! WARNING

**HAZARD OF
ELECTRICAL SHOCK
OR BURN.
CONTACT UTILITY
FOR SERVICE.**

CALL 748-555-5825 / 24 HOURS A DAY



This 4" x 6" sign costs just \$0.63 USD/\$0.79 CDN printed with MiniMark (Actual Size)

BATTERY CHARGER

PMC 7



This 2-1/4" x 6" label costs just \$0.47 USD/\$0.59 CDN printed with MiniMark (Actual Size)

R TO EXTR # 7

This 4" x 17" sign costs just \$1.78 USD/\$2.23 CDN printed with MiniMark

THIS IS NOT AN EXIT
PLANT ENTRANCE
FROM CDC



HOT WTR RET FROM BI

This 2-1/4" x 12" pipe marker costs just \$0.94 USD/\$1.18 CDN printed with MiniMark (Actual Size)

EXTINTOR DE
INCENDIOS



This 4" x 8" sign costs just \$0.84 USD/\$1.05 CDN printed with MiniMark (Actual Size)



MMA



LR #2

This 4" x 39" label costs just \$4.09 USD/\$5.11 CDN printed with MiniMark (Actual Size)

This 1-1/8" x 3" label costs just \$0.17 USD/\$0.21 CDN printed with MiniMark (Actual Size)

PK-208

ELECTRIX CO.

| | |
|-----------------|--------------|
| VOLTS | 480 |
| AMPS | 225 |
| CAT. NO. | 76823 |

This 2-1/4" x 5-1/2" label costs just \$0.43 USD/\$0.54 CDN printed with MiniMark (Actual Size)



This 2-1/4" x 12" pipe marker costs just \$0.94 USD/\$1.18 CDN printed with MiniMark (Actual Size)

MAXIMU

al Size)



MiniMark

LOCKOUT PROCEDURE FOR WINDER SERIAL #56009



The E-1 Disconnect is located on the West side of the machine. Turn Disconnect to the OFF position and lock out at E-1.

The P-1 Valve is located on the Front side of the machine. Turn Valve to the OFF position and lock out at P-1.



The G-1 Valve is located on the Top side of the machine. Turn Valve to the OFF position and lock out at G-1.

This 4" x 8" procedure sign costs just \$0.84 USD/\$1.05 CDN printed with MiniMark

TR TO EAST WHSE



Meeting every need for faster, better Facility ID

HANDIMark



On-the-spot-ID

The HandiMark® Portable Label Maker lets you create custom labels wherever you need them – in the office, throughout the plant, or even in the field – all on-the-spot and at a fraction of the cost of custom printed or engraved labels.



GLOBALMark²
INDUSTRIAL LABEL MAKER



Need Color Signs Fast?

The GlobalMark® Industrial Label Maker offers multi-color signs and labels, and die cut shapes and letters up to 4" wide – just touch the screen, print, and your label is ready to go. Available in MultiColor, MonoColor, and Color & Cut systems for the flexibility and features you need.



POWERMark
sign and label maker



When it needs to be BIG

With the PowerMark® Sign and Label Maker, you can print multi-color signs and labels up to 10" wide for big, bold messages that increase safety and improve productivity throughout your facility.



Both GlobalMark and PowerMark printers allow you to select from a wide variety of specialty materials including glow-in-the-dark, tagstock, reflective, and magnetic. Find more information at www.bradyid.com.

USA
Customer Service: 1-888-272-3946
Inside Sales: 1-888-311-0775
www.BradyID.com

Canada
Customer Service: 1-800-263-6179
www.BradyCanada.ca

Mexico
Customer Service: 1-800-262-7777
Inside Sales: 1-800-262-7777 ext 177
www.BradyLatinAmerica.com



Contact Brady Today

schedule your **FREE** appointment to set up your new printer and software – www.bradyid.com/setupservice or call 1-800-643-8766 and select menu option 4.

 **BRADY**
WHEN PERFORMANCE MATTERS MOST™



© 2007 Brady Worldwide, Inc. 01-07-AA-10K
All Rights Reserved.
Printed in U.S.A.