


# ALBION®

## CASTERS AND WHEELS

# Heavy Duty Casters Large Plate

- Double Row Swivel Raceways
- Heat Treated and Factory Lubricated Raceways
- Yellow Zinc Chromate Finish

**Applications:** Platform Trucks, Warehouse Trucks, Material Handling Containers, Dollies, Waste Disposal Trucks, Floor Trucks, Shop Carts



932PD05201SL




932MD05201SB



932TM05201ST



932CA06201R



**Overall Size:** 5" x 5-1/2"  
**Hole Soacing:** 4-1/8" x 4-1/2"  
**Bolt Dia.:** 3/8"

Wheel Dia. (In.)	Tread Width (In.)	Load Rating (lbs.)	Overall Height (In.)	Swivel Part Number	Swivel W/Brake Part Number	Total-Lock Part Number	Directional-Lock Part Number	Rigid Part Number
<b>Soft Rubber Tread on Aluminum Core Wheel (Roller Bearing)</b>								
5	2	350	6-1/2	932MD05201S	932MD05201SB			932MD05201R
6	2	410	7-1/2	932MD06201S	932MD06201SB			932MD06201R
8	2	500	9-1/2	932MD08201S	932MD08201SB			932MD08201R
<b>Polyurethane Tread on Aluminum Core Wheel (Roller Bearing)</b>								
5	2	1050	6-1/2	932PD05201S		932PD05201ST	932PD05201SL	932PD05201R
6	2	1200	7-1/2	932PD06201S		932PD06201ST	932PD06201SL	932PD06201R
8	2	1200	9-1/2	932PD08201S		932PD08201ST	932PD08201SL	932PD08201R
<b>Phenolic Wheel (Roller Bearing)</b>								
5	2	1000	6-1/2	932TM05201S		932TM05201ST		932TM05201R
6	2	1200	7-1/2	932TM06201S		932TM06201ST		932TM06201R
8	2	1200	9-1/2	932TM08201S		932TM08201ST		932TM08201R
<b>Semi-Steel Wheel (Roller Bearing)</b>								
5	2	1000	6-1/2	932CA05201S	932CA05201SB	NA	NA	932CA05201R
6	2	1200	7-1/2	932CA06201S	932CA06201SB	NA	NA	932CA06201R
8	2	1200	9-1/2	932CA08201S	932CA08201SB	NA	NA	932CA08201R
<b>Polyurethane Tread on Aluminum Core Wheel (Roller Bearing) NSF Certified</b>								
5	2	750	6-1/2	932PD05201SN	NA	NA	NA	932PD05201RN
6	2	900	7-1/2	932PD06201SN	NA	NA	NA	932PD06201RN
8	2	900	9-1/2	932PD08201SN	NA	NA	NA	932PD08201RN