

PIG® Green Ham-O® Absorbent Mat Roll

#MAT123 - Heavy-weight • 16" x 150' • 2 rolls



Distinctive Ham-O top conceals absorbed leaks and drips. Scuff-resistant top layer stands up to foot traffic in aisles and walkways.

- Lasts 2X longer than ordinary mats for fewer change-outs, absorbs everything, works everywhere; that's why more plants worldwide use PIG Mat than any other brand
- Absorbed leaks and drips blend right in; Exclusive "hamouflage" top layer saves on product and disposal costs; absorbed grime is invisible, so you'll leave mat in place longer and save money!
- Fast-wicking dimple pattern transfers liquids from the top layer into the absorbent inner layers; spills disappear in seconds
- Tough, scuff-resistant, spunbond top layer stands up to heavy foot traffic; won't rip, tear, fray or create a trip hazard, even when saturated
- Under the Ham-O top layer is the proven eight-layer, 100% polypropylene construction of PIG Mat, the strongest mat on the market!
- Absorbs most common industrial liquids - oils, water, solvents, coolants and more
- Flame-resistant material won't burn immediately like cellulose mats; melts when exposed to high heat while on the job
- Can be wrung out and incinerated after use to reduce waste or for fuels blending
- Rolls are ideal for walkways and large areas to soak up leaks and overspray
- Easy-tear perforations let you take only what you need, so you use less mat and save money
- Heavy-weight construction delivers greater durability and absorbency for demanding tasks and large-volume cleanups

Always in stock. Ships within 24 hours.



By Phone:
1-855-493-HOGS

Online:
newpig.com

Email:
hothogs@newpig.com

New Pig

One Pork Avenue • Tipton PA 16684-0304
© 2014 New Pig Corporation. All rights reserved.
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: MAT123 - Pg 1 of 2

MAT123 Specifications

Color:	Green & Tan
Dimensions:	16" W x 150' L
Mat Weight:	Heavy-weight
Fluids Absorbed:	Oils, Coolants, Solvents & Water
Recycled Content:	40% Recycled Content
Absorbency:	Up to 47.4 gal. per bag
Absorbency per:	Up to 23.7 gal. per roll
Dispenser:	No
Perforated:	Every 10" Lengthwise
Poly-Backing:	No
UV Resistant:	No
Sold as:	2 rolls per bag
Weight:	36 lbs.
# per Pallet:	12
Composition:	100% polypropylene
UNSPSC:	47131901

Technical Information

Warnings & Restrictions:

HAM-O® Mat Notice
Not recommended for absorbing solvents or corrosive liquids that may affect the printed pattern.

Regulations and Compliance:

29 CFR 1910.22(a)(2) - Floors in the workplace should be, "maintained in a clean and, so far as possible, a dry condition."

Technical Documents:

(Available at newpig.com)
Product Data Sheet (PDS)
Safety Data Sheet (SDS)
Chemical Compatibility (CCG)



MAT123 Metric Equivalent

Dimensions:	40.6cm W x 46m L
Absorbency:	Up to 179.4 L per bag
Absorbency per:	Up to 89.7 L per roll
Weight:	16.3 kg



New Pig

By Phone:
1-855-493-HOGS

Online:
newpig.com

Email:
hothogs@newpig.com