

**CAROL[®]
BRAND**

FrogHide[®]

ULTRA FLEX[®]

The ultimate outdoor extension cord
designed to take on
the toughest applications



Resists oil, ozone, chemicals, abrasion, harsh weather conditions and extreme temperatures.

 **General Cable**

**CAROL
BRAND**

FrogHide[®]
ULTRA FLEX[®]

Ultra Flexible Rubber... Heavy-Duty Outdoor Cord



Here's a premium rubber outdoor cord with new levels of flexibility and durability.

FrogHide is more than a funny name. It's the most durable rubber outdoor cord on the market. And the most flexible, even in the coldest conditions.

The three-conductor grounded FrogHide extension cord uses the most advanced rubber technology available anywhere. A technology that molecularly bonds cap and connector to the cord to prevent cord pull-out. And a heavy-duty strain relief is built-in for lasting strength, even in rough applications.

FrogHide's improved electrical connections ensure more contact area between blades and receptacles, resulting in longer cord life. There's more: FrogHide's distinctive green color is complemented by an exclusive personal identification system and a limited lifetime warranty.

Use FrogHide anywhere:

- Indoor & Outdoor Applications
- Hot & Cold Temperatures
- Abusive Environments
- Harsh Weather Conditions

FrogHide's like no other outdoor cord. It is resistant to oil, water, ozone and chemicals. It out-performs other extension cords in low and room temperatures, and does not soften when exposed to heat.

Flexible

FrogHide cords are constructed to be more flexible than any other outdoor cord... and to stay flexible in any condition or environment.

Durable

FrogHide's molecularly bonded cord and heavy-duty strain relief provide long-lasting strength, even in the roughest of applications. Its improved electrical box connections ensure more contact area between blades and receptacles, resulting in longer cord life.

Identifiable

FrogHide's unique personal ID system lets you write your name with a permanent marker on the cord, then slide the heat-shrink sleeve over your name and apply heat with a heat gun or other concentrated heat source.

FEATURES

Ultra Flex Cord	FrogHide's state-of-the-art rubber technology provides for more flexibility than any cord on the market.
Molecularly Bonded Cap And Connector	FrogHide cord is molecularly bonded to the ends with a heavy-duty strain relief built-in for lasting strength. There's no more worry about cord pull-out.
Improved Electrical Connections	More contact area between blades and box contact receptacles ensure longer cord life.
Distinctive Green Color	FrogHide looks like no other cord. Its bright green color is easy to see on the job — anytime, anywhere.
Identification System	It's simple to permanently mark your FrogHide cord with your name.
Limited Lifetime Warranty	We are so satisfied with the FrogHide cord we guarantee you will be too.
Specifications	FrogHide is UL Listed and meets all appropriate OSHA requirements.

Extension Cord Performance Guide

	FrogHide	Lighted Yellow	All Weather	Round Orange
Low Temperature Flex	Excellent	Good	Very Good	Fair
Room Temperature Flex	Excellent	Very Good	Fair	Good
Oil Resistance	Excellent	Very Good	Very Good	Fair
Cap/Cord Bonding	Excellent	Very Good	Excellent	Good
Abrasion Resistance	Very Good	Very Good	Very Good	Very Good
Chemical Resistance	Excellent	Very Good	Very Good	Very Good
Heat Softening	Excellent	Fair	Fair	Fair
Water Resistance	Excellent	Excellent	Good	Good
Flame Resistance	Very Good	Very Good	Very Good	Very Good

Flexibility

- FrogHide
- Lighted Yellow
- All Weather
- Round Orange

Measured at 5° F

Deflection




Electrical Contacts

Cycle 45 minutes on with 25 amps of current and 15 minutes off.

- New Box Contact
- Edge Contact

Temperature



**CAROL
BRAND**

FrogHide®

ULTRA FLEX®

The
ultimate
outdoor
extension
cord.



MASTER CARTONS

CATALOG NUMBER	DESCRIPTION	CARTON QTY.	UPC CODE
06425.63.06	25' 14/3 SJOW	10	079407 064250
06450.63.06	50' 14/3 SJOW	6	079407 064502
06400.63.06	100' 14/3 SJOW	4	079407 064007
06225.61.06	25' 12/3 SJOW	6	079407 062256
06250.61.06	50' 12/3 SJOW	4	079407 062508
06200.61.06	100' 12/3 SJOW	2	079407 062003

FrogHide ULTRA FLEX is designed to take on the toughest applications: resists oil, ozone, chemicals, abrasion, harsh weather conditions and temperature extremes.

 **General Cable** 4 Tesseneer Drive, Highland Heights, Kentucky 41076

GENERAL CABLE, CAROL BRAND, FROGHIDE, ULTRA FLEX, their logos and the distinctive green color are trademarks of General Cable Technologies Corporation.

©2007, General Cable Technologies Corporation.
Highland Heights, KY 41076
All rights reserved.

Phone: 1-800-243-8020
Fax: 1-859-572-9262
www.generalcable.com

Form No. CAR-0068-R1007