


SEALED LEAD ACID BATTERIES

Maintenance-free rechargeable batteries.



KEY PRODUCT ATTRIBUTES

- Maintenance-free sealed battery
- Operational in any position or direction without leakage
- Approved shipping as non-hazardous and non-spillable material
- Available in 12V batteries with 5 years useful life
- Available in 6V batteries with 3 to 5 years useful life
- Suitable for use in emergency lighting, UPS systems and standby power operations



ITEM NO.	VOLTAGE	BATTERY CAPACITY	DEPTH	WIDTH	HEIGHT	TERMINAL CONNECTION
ABS						
5EFG3	4	3.3Ah	3 ⁹ / ₁₆ "	1 ³ / ₈ "	2 ¹ / ₂ "	0.187" Male Tab
2UKL1		4.5Ah	1 ⁷ / ₈ "	1 ⁷ / ₈ "	4 ³ / ₁₆ "	0.187" Male Tab
5EFE7		4.5Ah	1 ⁷ / ₈ "	1 ⁷ / ₈ "	4 ¹ / ₈ "	0.250" Male Tab
5EFE8		9Ah	4"	1 ³ / ₄ "	4"	0.250" Male Tab
5EFE9		10Ah	4"	1 ¹⁵ / ₁₆ "	4"	0.187" Male Tab
5EFF0		1Ah	1 ¹⁵ / ₁₆ "	1 ⁵ / ₈ "	2 ³ / ₁₆ "	0.187" Male Tab
2UKH1		1.2Ah	1 ⁵ / ₁₆ "	3 ¹³ / ₁₆ "	2 ¹ / ₄ "	0.187" Male Tab
2UKL2		2.8Ah	1 ⁵ / ₁₆ "	2 ⁵ / ₈ "	4 ³ / ₁₆ "	0.187" Male Tab
5EFF1		3.5Ah	5 ¹ / ₄ "	1 ³ / ₈ "	2 ⁹ / ₁₆ "	0.187" Male Tab
2UKJ2		4Ah	1 ⁷ / ₈ "	2 ³ / ₄ "	4 ¹ / ₄ "	0.187" Male Tab
5EFF2	4.5Ah	2 ³ / ₄ "	1 ⁷ / ₈ "	4 ³ / ₁₆ "	0.187" Male Tab	
5EFF3	5Ah	2 ¹¹ / ₁₆ "	2 ⁵ / ₈ "	4 ³ / ₄ "	0.187" Male Tab	
5EFF4	5Ah	2 ¹¹ / ₁₆ "	2 ⁵ / ₈ "	3 ¹⁵ / ₁₆ "	Spring	
5EFG4	5Ah	2 ³ / ₄ "	1 ⁷ / ₈ "	4 ³ / ₁₆ "	0.187" Male Tab	
2UKJ6	6	7Ah	1 ⁵ / ₁₆ "	5 ¹⁵ / ₁₆ "	3 ¹⁵ / ₁₆ "	0.187" Male Tab
5EFF5	7Ah	5 ¹⁵ / ₁₆ "	1 ³ / ₈ "	3 ¹⁵ / ₁₆ "	0.187"(-)/0.250"(+) Male Tab	
2UKK3	8.5Ah	1 ⁹ / ₁₆ "	5 ¹⁵ / ₁₆ "	3 ¹⁵ / ₁₆ "	0.187" Male Tab	
5EFF6	9Ah	3 ⁷ / ₈ "	2 ³ / ₁₆ "	4 ¹ / ₂ "	0.187" Male Tab	
2UKH2	10Ah	2"	5 ¹⁵ / ₁₆ "	3 ⁷ / ₈ "	0.187" Male Tab	
2UKK6	12Ah	2"	5 ¹⁵ / ₁₆ "	3 ⁷ / ₈ "	0.250" Male Tab	
5EFF7	14Ah	4 ³ / ₁₆ "	2 ³ / ₄ "	5 ¹ / ₂ "	0.187"(-)/0.250"(+) male tab	
24A822	20Ah	3 ⁹ / ₃₂ "	6 ³ / ₁₆ "	4 ⁵⁹ / ₆₄ "	0.236 Diameter hole	
24A823	36Ah	3 ⁷ / ₁₆ "	6 ¹¹ / ₃₂ "	6 ²¹ / ₃₂ "	F2,0.250 male tab	
24A824	120Ah	5 ³ / ₆₄ "	11 ¹ / ₆₄ "	7 ⁶³ / ₆₄ "	M6	
24A825	8	3.2Ah	1 ⁷ / ₁₆ "	5 ⁹ / ₃₂ "	2 ²³ / ₃₂ "	F1,0.187 male tab
5EFG5	4.2Ah	3 ³ / ₄ "	1 ¹³ / ₁₆ "	3 ⁷ / ₈ "	0.187" Male Tab	



ITEM NO.	VOLTAGE	BATTERY CAPACITY	DEPTH	WIDTH	HEIGHT	TERMINAL CONNECTION
2UKG8	12	0.8Ah	1 ⁹ / ₁₆ "	3 ³ / ₄ "	2 ⁷ / ₁₆ "	2 Pin
2UKG9		1.2Ah	1 ¹¹ / ₁₆ "	3 ¹³ / ₁₆ "	2 ¹ / ₄ "	0.187" Male Tab
5EFG6		2.2Ah	2 ³ / ₄ "	1 ⁷ / ₈ "	4 ³ / ₁₆ "	0.187" Male Tab
5EFF8		2.3Ah	6 ¹⁵ / ₁₆ "	1 ³ / ₈ "	2 ⁵ / ₈ "	0.187" Male Tab
5EFF9		2.6Ah	6 ¹⁵ / ₁₆ "	1 ³ / ₈ "	2 ⁵ / ₈ "	0.187" Male Tab
5EFG0		3.4Ah	5 ¹ / ₄ "	2 ⁵ / ₈ "	2 ⁵ / ₈ "	0.187" Male Tab
2UKJ1		4Ah	2 ³ / ₄ "	3 ¹ / ₂ "	4 ³ / ₁₆ "	0.187" Male Tab
2UKJ3		5Ah	2 ³ / ₄ "	3 ¹ / ₂ "	4 ³ / ₁₆ "	0.187" Male Tab
2UKJ9		5Ah	2 ³ / ₄ "	3 ¹ / ₂ "	4 ³ / ₁₆ "	0.250" Male Tab
5EFG7		5.4Ah	5 ¹⁵ / ₁₆ "	1 ¹⁵ / ₁₆ "	3 ⁷ / ₈ "	0.187" Male Tab
2UKJ4		7Ah	2 ⁹ / ₁₆ "	5 ¹⁵ / ₁₆ "	3 ¹⁵ / ₁₆ "	0.187" Male Tab
5EFG8		7.5Ah	5 ¹⁵ / ₁₆ "	2 ⁹ / ₁₆ "	3 ⁷ / ₈ "	0.187" Male Tab
5EFH6		7.5Ah	5 ¹⁵ / ₁₆ "	2 ⁹ / ₁₆ "	3 ⁷ / ₈ "	0.250" Male Tab
2UKK2		8.5Ah	2 ⁹ / ₁₆ "	5 ¹⁵ / ₁₆ "	3 ³ / ₄ "	0.187" Male Tab
5EFG9		10Ah	5 ¹⁵ / ₁₆ "	2 ⁹ / ₁₆ "	4 ³ / ₁₆ "	0.197" Diameter Hole
5EFH0		10Ah	5 ¹⁵ / ₁₆ "	3 ⁷ / ₈ "	3 ¹⁵ / ₁₆ "	0.250" Male Tab
2UKH3		12Ah	4"	5 ¹⁵ / ₁₆ "	3 ¹⁵ / ₁₆ "	0.250" Male Tab
2UKH5		17Ah	3"	7 ³ / ₄ "	6 ⁹ / ₁₆ "	0.197" Diameter Hole
2UKK8		20Ah	7 ¹⁵ / ₆₄ "	3 ¹ / ₁₀ "	6 ⁹ / ₁₆ "	0.197" Diameter Hole
2UKL3		24Ah	7"	6 ⁵ / ₈ "	5"	0.553" Male Tab
5EFG1		28Ah	6 ⁵ / ₈ "	4 ¹⁵ / ₁₆ "	7 ¹ / ₈ "	0.197" Diameter Hole
2UKL4		33Ah	5 ¹ / ₈ "	7 ³ / ₄ "	7-1/6"	0.197" Diameter Hole
5EFH2		33Ah	7 ¹¹ / ₁₆ "	5 ³ / ₁₆ "	7 ¹ / ₁₆ "	M6
5EFH3		38Ah	7 ¹¹ / ₁₆ "	6 ⁹ / ₁₆ "	6 ⁷ / ₈ "	M6
5EFG2		40Ah	7 ¹¹ / ₁₆ "	6 ⁹ / ₁₆ "	7"	0.197" Diameter Hole
24A826		50Ah	5 ¹³ / ₆₄ "	10 ⁷ / ₆₄ "	7 ⁷ / ₈ "	M6
2UKL5		55Ah	5 ⁷ / ₁₆ "	9"	9"	0.197" Diameter Hole
5EFH4		55Ah	9"	5 ⁷ / ₁₆ "	9"	M6
2UKL6		65Ah	6 ¹ / ₂ "	13 ⁷ / ₈ "	6 ⁷ / ₈ "	0.197" Diameter Hole
2UKL7		75Ah	6 ⁵ / ₈ "	10 ³ / ₁₆ "	9"	0.197" Diameter Hole
5EFH5	75Ah	10 ¹ / ₄ "	6 ⁹ / ₁₆ "	9"	M6	
24A827	80Ah	6 ³⁹ / ₆₄ "	10 ¹³ / ₆₄ "	8 ⁷ / ₁₆ "	M6	
2UKL8	100Ah	6 ³ / ₄ "	12 ¹⁵ / ₁₆ "	9 ⁹ / ₁₆ "	0.315" Diameter Hole	
5EFH1	120Ah	16"	6 ⁷ / ₈ "	9 ³ / ₁₆ "	0.315" Diameter Hole	
24A828	150Ah	6 ¹¹ / ₁₆ "	19 ³ / ₃₂ "	9 ²⁹ / ₆₄ "	M8	
FLAME-RETARDANT ABS						
2UKK4	6	8.5Ah	1 ⁵ / ₁₆ "	5 ¹⁵ / ₁₆ "	3 ¹⁵ / ₁₆ "	0.187" Male Tab
2UKK7		12Ah	2"	5 ¹⁵ / ₁₆ "	3 ⁷ / ₈ "	0.250" Male Tab
2UKK1		5Ah	2 ³ / ₄ "	3 ¹ / ₂ "	4 ³ / ₁₆ "	0.250" Male Tab
2UKJ5	12	7Ah	2 ⁹ / ₁₆ "	5 ¹⁵ / ₁₆ "	3 ¹⁵ / ₁₆ "	0.187" Male Tab
2UKK5		8.5Ah	2 ⁹ / ₁₆ "	5 ¹⁵ / ₁₆ "	3 ¹⁵ / ₁₆ "	0.187" Male Tab
2UKH4		12Ah	4"	5 ¹⁵ / ₁₆ "	3 ¹⁵ / ₁₆ "	0.250" Male Tab
2UKH6		17Ah	3"	7 ³ / ₄ "	6 ⁹ / ₁₆ "	0.197" Diameter Hole
2UKH7		2.3Ah	1-5/13"	6 ¹⁵ / ₁₆ "	2 ⁵ / ₈ "	0.187" Male Tab
2UKH8		3.3Ah	2 ⁹ / ₁₆ "	5 ⁹ / ₃₂ "	2 ⁵ / ₈ "	0.187" Male Tab
2UKK9		20Ah	3"	7 ³ / ₄ "	6 ⁹ / ₁₆ "	0.197" Diameter Hole
2UKJ7		28Ah	5"	6 ⁵ / ₈ "	7 ³ / ₁₆ "	10-32
2UKJ8		40Ah	6 ¹ / ₂ "	7 ³ / ₄ "	6 ⁷ / ₈ "	10-32