



1200 SERIES ELECTRIC PIZZA OVEN REPLACEMENT PARTS LIST



EFFECTIVE JULY 11, 2011

BLODGETT OVEN COMPANY, 44 Lakeside Avenue, Burlington, Vermont 05401 USA

Telephone: (802) 658-6600 Fax: (802) 860-3732

www.blodgett.com

P/N 53033

Superseding All Previous Parts Lists.

The Company reserves the right to make substitution in the event that items specified are not available.

ERRORS: Descriptive and/or typographic errors are subject to correction.

www.blodgett.com

IMPORTANT: When ordering parts, please provide the model, gas type and serial number of the oven. The identification plate is located on the left side of the combustion compartment and, also, above the control panel under the ledge.



ASAP Distributor Required Stocking Parts
Doors Are Not Returnable
Item Is Too Large For UPS

ELECTRICAL COMPONENTS

Ref. No.	Part No.	Description
	10559	Transformer 480/240V to 120V
	15549	Indicator Light 125V, Red Rect.
	9086	Fuse, 2 AMP, Class G
	11267	Fuseholder, Class G
	17469	Knob, only (for heater switch)
☑	5279	Thermostat, KX-38-36 (140-550°)
	11224	Dial, Fahrenheit (For 5279)
	9062	Thermostat, KX-268-24 (200-650°) (Thermostat to 700° no longer available)
	19262	Dial, Fahrenheit (For 9062)
	9630	Dial, Centigrade (For 9062)
☑	15956	Timer, 60 Min. Rhodes
	16030	Knob, Black
☑	20349	Buzzer & Terminals, 120V
	16820	Dial, Timer 1HR Cook
☑	20350	Buzzer & Terminals, 240V
	11427	Timer, 6 HR
	3574	Terminal Block 65AMP, 600V
	11203	Circuit Breaker, 60AMP
	90588	Contactoer w/ Hardware
☑	5147	Timer, 60 Min. Mechanical w/Bell
	34483	Dial, Timer 60 Min. Mechanical
	34484	Knob, Timer 60 Min. Mechanical
	21430	Axial Fan 230V
	33095	Terminal Block, 6 Pole CE

BAKING COMPARTMENT COMPONENTS

Ref. No.	Part No.	Description
	10233	Handle, Door 21" (After 7/77)
	9038	Handle, Door 20" (Before 7/77)
	8342	Arm Assy, Door LH Support
	8343	Arm Assy, Door RH Support
	8338	Hinge Pin, Door RH
NOTE:		Hinge Pin, Door LH is a welded/non-replaceable part.

BAKING COMPARTMENT COMPONENTS-CONT'D.

Ref. No.	Part No.	Description
	3840	Retainer Ring, Door
	3652	Hinge Assy, Door Link
	11694	Door Washer (Set of 10)
*	8353	Steel Deck Assy.
*	35058	Ultra Rokite Deck Assy

ELEMENTS

Ref. No.	Part No.	Description
	18956	Element, 208V
	19527	Element, 208V "L" Shape
	8914	Element, 220V
	10229	Element, 220V "L" Shape
	8915	Element, 240V
	10230	Element., 240V "L" Shape
	8918	Element, 480V
	10240	Element, 480V "L" Shape
	20569	Element Jumper, with low cold end junction (used with 208, 230, 240V)

EXTERIOR COMPONENTS

Ref. No.	Part No.	Description
	7842	Legs, 7", S/S w/Bolts (Set of 4)
	18693	Legs, 19" S/S w/ Bolts (Set of 4)
17831		Legs, 32" S/S w/Bolts (Set of 4)
	7846	Legs, 27 1/2" S/S w/Bolts (Set of 4)
	30822	Legs w/ Casters, 7" w/ Bolts (Set of 4) Black
	31588	Legs w/ Casters, 12" w/ Bolts (Set of 4) Black
	30823	Legs w/ Casters, 19" w/ Bolts (Set of 4) Black
	30824	Legs w/ Casters, 27" w/ Bolts (Set of 4) Black
	20462	Bottom, Louvered Trim
	11255	Nameplate, BLODGETT 12 3/4"