

Multi-Gen®

The better alternative to plastic disposable generator probes

Multi-Gen® generator probes are the better alternative to disposable plastic generator probes. This unique equipment is a reusable 7mm diameter generator probe manufactured from superior 316 stainless steel and PTFE, which allows for homogenizing samples without cross contamination and without the need to stop and clean a generator between samples. A Multi-Gen generator probe can quickly lock into the special Multi-Gen Adapter to provide hands-free ejection of the probe, minimizing the chance of accidental contamination. Multi-Gen generator probes are offered in multi-packs of 12 or 24 for convenience.

Advantages over plastic disposable generator probes:

First advantage, Multi-Gen generator probes can process more difficult samples, including tough tissues.

Second advantage, Multi-Gen generator probes can be sterilized by any method, including flaming and autoclaving.

Third advantage, Multi-Gen generator probes are more economical because of its ability to be reused an unlimited number of times not like plastic disposable generator probes

Multi-Gen 7 Features:

- Flat bottom design – ideal for liquid and soft samples
- Shaft length – best for microtubes to 5ml tubes

Multi-Gen 7XL Features:

- Open slotted tooth design – ideal for the softest to the toughest of samples
- Longer shaft, approximately 115mm – perfect for sample volumes from microtubes to 50ml tubes

Multi-Gen 7 and 7XL COMPONENTS AVAILABLE INDIVIDUALLY

Item No.	Description
07-07200	Multi-Gen Adapter Required when using either Multi-Gen generator
02-070MG-12	Multi-Gen 7 Generators (12/package)
02-070MG-24	Multi-Gen 7 Generators (24/package)
02-070MGXL-12	Multi-Gen 7XL Generators (12/package)
80-00218	Multi-Gen Ejector Clamp Assembly For use with 80-00200 PRO200 Stand Assembly (see page 3) and Multi-Gen 7 generators only. Includes: Post clamp assembly, cross rod assembly, ejector collar
03-11703P	PTFE Bearings Replacement PTFE bearings for use in Multi-Gen 7 generators

Most recommended motor unit for use with the Multi-Gen 7:

01-01200	PRO200 Homogenizer 120v homogenizer (see page 3)
01-02200	PRO200 Homogenizer 220v homogenizer (see page 3)
80-00200	PRO200 Stand Assembly 7 x 10 in. vinyl-padded base with easy-lift mechanism (see page 3)

NEXT-DAY DELIVERY ON THIS ITEM and most parts and accessories

www.proscientific.com

PRO Multi-Gen 7 and 7XL

Tougher than disposable generators – and more economical



Multi-Gen 7 contains 7mm stainless steel generators in convenient 12- or 24-count packages



Multi-Gen 7XL (top) and 7 generators cover the spectrum of sample volumes.



Multi-Gen 7XL is a package of 12 7mm open-slotted generators

Order toll-free: **1-800-5-THE PRO** (1-800-584-3776)