



Rittal – The System.

Faster – better – everywhere.

Rittal Corporation – Wallmount Industrial Enclosures

Rittal wallmount enclosures provide the protection, flexibility and value that translate to reliable and lasting solutions for today's intensive "return on investment" business approach. That's why wallmount enclosures are engineered to be the best in the world when it comes to form, function and value for the money. Readily available from Grainger in all of the most popular sizes, protection categories and configurations, unique design features like foamed-in-place gasketing and knife-edge perimeters are examples of Rittal's ability to provide innovative, durable, quality enclosure solutions at affordable prices.

NEMA 3R, 4 & 12 Carbon Steel Wallmount Enclosure

Grainger No.	Rittal No.	Dimensions H x W x D
5ENF7	WM121206NC	12 x 12 x 6
5AAA2	WM161206NC	16 x 12 x 6
5AAC7	WM161606NC	16 x 16 x 6
5AAA5	WM161208NC	16 x 12 x 8
5AAD3	WM201608NC	20 x 16 x 8
5AAD6	WM202008NC	20 x 20 x 8
5AAD9	WM242008NC	24 x 20 x 8
5AAE5	WM242408NC	24 x 24 x 8
5AAF1	WM302408NC	30 x 24 x 8
5AAG0	WM303008NC	30 x 30 x 8
5AAG3	WM363008NC	36 x 30 x 8
5AAE2	WM242010NC	24 x 20 x 10
5AAF4	WM302410NC	30 x 24 x 10
5AAG6	WM363010NC	36 x 30 x 10
5AAE8	WM242412NC	24 x 24 x 12
5AAF7	WM302412NC	30 x 24 x 12
5AAG9	WM363012NC	36 x 30 x 12
5AAH2	WM363612NC	36 x 36 x 12
5AAH5	WM483612NC	48 x 36 x 12
5AAH8	WM603612NC	60 x 36 x 12

Note: Enclosure includes mounting panel.

Accessories

Grainger No.	Rittal No.	Description
5AAJ1	1590.000	Wallmounting Brackets, Sheet Steel, Zinc-plated, Passivated
5AAJ2	1594.000	Wallmounting Brackets, 304 Stainless Steel
5AAJ3	WMSMB	Slotted Wallmount Bracket, Zinc-plated
5AAJ4	WMSMB6	Slotted Wallmount Bracket, 316 Stainless Steel
5AAJ5	2576.000	Thumb Turn Handle with Key Lock
5AAJ6	WMQTPLS6	Thumb Turn Handle, Padlockable, 316L Stainless Steel

NEMA 12 Carbon Steel 2 Door Wallmount

Grainger No.	Rittal No.	Dimensions H x W x D
6VJV2	WM244208NC	24 x 42 x 8
6VJV3	WM304210NC	30 x 42 x 10
6VJV4	WM304810NC	30 x 48 x 10
6VJV5	WM364212NC	36 x 42 x 12
6VJV6	WM364812NC	36 x 48 x 12
6VJV7	WM366012NC	36 x 60 x 12
6VJV8	WM426012NC	42 x 60 x 12
6VJV9	WM484812NC	48 x 48 x 12

Note: Enclosure includes mounting panel.

NEMA 4 & 12 Carbon Steel Wallmount for Disconnect Applications

Grainger No.	Rittal No.	Dimensions H x W x D
6VJX8	WM242608XC	24 x 26 x 8
6VJY0	WM363210XC	36 x 32 x 10
6VJY1	WM363212XC	36 x 32 x 12
6VJY2	WM423212XC	42 x 32 x 12
6VJY3	WM483812XC	48 x 38 x 12
6VJY4	WM483816XC	48 x 38 x 16

Note: Enclosure includes mounting panel.

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



Rittal Corporation – Wallmount Industrial Enclosures

NEMA 4X Stainless Steel 304 Wallmount Enclosure

Grainger No.	Rittal No.	Dimensions H x W x D
5ENF8	WM121206N4	12 x 12 x 6
5AAA3	WM161206N4	16 x 12 x 6
5AAC8	WM161606N4	16 x 16 x 6
5AAD1	WM201606N4	20 x 16 x 6
5AAA6	WM161208N4	16 x 12 x 8
5AAD4	WM201608N4	20 x 16 x 8
5AAD7	WM202008N4	20 x 20 x 8
5AAE6	WM242408N4	24 x 24 x 8
5AAF2	WM302408N4	30 x 24 x 8
5AAG1	WM303008N4	30 x 30 x 8
5AAG4	WM363008N4	36 x 30 x 8
5AAE3	WM242010N4	24 x 20 x 10
5AAG7	WM363010N4	36 x 30 x 10
5AAE9	WM242412N4	24 x 24 x 12
5AAF8	WM302412N4	30 x 24 x 12
5AAH0	WM363012N4	36 x 30 x 12
5AAH3	WM363612N4	36 x 36 x 12
5AAH6	WM483612N4	48 x 36 x 12
5AAH9	WM603612N4	60 x 36 x 12

Note: Enclosure includes mounting panel.

NEMA 4X Stainless Steel 316L Wallmount Enclosure

Grainger No.	Rittal No.	Dimensions H x W x D
5ENF9	WM121206N6	12 x 12 x 6
5AAA4	WM161206N6	16 x 12 x 6
5AAC9	WM161606N6	16 x 16 x 6
5AAD2	WM201606N6	20 x 16 x 6
5AAA7	WM161208N6	16 x 12 x 8
5AAD5	WM201608N6	20 x 16 x 8
5AAD8	WM202008N6	20 x 20 x 8
5AAE7	WM242408N6	24 x 24 x 8
5AAF3	WM302408N6	30 x 24 x 8
5AAG2	WM303008N6	30 x 30 x 8
5AAG5	WM363008N6	36 x 30 x 8
5AAE4	WM242010N6	24 x 20 x 10
5AAG8	WM363010N6	36 x 30 x 10
5AAF0	WM242412N6	24 x 24 x 12
5AAF9	WM302412N6	30 x 24 x 12
5AAH1	WM363012N6	36 x 30 x 12
5AAH4	WM363612N6	36 x 36 x 12
5AAH7	WM483612N6	48 x 36 x 12
5AAJ0	WM603612N6	60 x 36 x 12

Note: Enclosure includes mounting panel.

NEMA 4X Stainless Steel 304 Wallmount, Slope Top

Grainger No.	Rittal No.	Dimensions H x W x D
6VJY7	WMS161208N4	16 x 12 x 8
6VJY8	WMS161608N4	16 x 16 x 8
6VJZ0	WMS201612N4	20 x 16 x 12
6VJZ1	WMS202008N4	20 x 20 x 8
6VJZ3	WMS242408N4	24 x 24 x 8
6VJZ6	WMS302412N4	30 x 24 x 12
6VKA0	WMS363016N4	36 x 30 x 16
6VKA2	WMS483616N4	48 x 36 x 12
6VKA3	WMS603616N4	60 x 36 x 12

Note: Enclosure includes mounting panel.

NEMA 4X Stainless Steel 304 Wallmount for Disconnect Applications

Grainger No.	Rittal No.	Dimensions H x W x D
6VJW0	WM242608X4	24 x 26 x 8
6VJW1	WM363208X4	36 x 32 x 8
6VJW3	WM363212X4	36 x 32 x 12
6VJW4	WM423212X4	42 x 32 x 12
6VJW6	WM483816X4	48 x 38 x 16

Note: Enclosure includes mounting panel.

NEMA 4X Stainless Steel 316L Wallmount for Disconnect Applications

Grainger No.	Rittal No.	Dimensions H x W x D
6VJW9	WM242608X6	24 x 26 x 8
6VJX0	WM363208X6	36 x 32 x 8
6VJX2	WM363212X6	36 x 32 x 12
6VJX3	WM423212X6	42 x 32 x 12
6VJX5	WM483816X6	48 x 38 x 16

Note: Enclosure includes mounting panel.