



Rittal – The System.

Faster – better – everywhere.

Rittal Corporation – Freestanding Industrial Enclosures

The Rittal TS8 is the premier modular enclosure available in the world today. The strength and flexibility of the TS8 come from its robust 16-fold, tubular frame that features a 25 mm hole pattern that allows components and accessories to be mounted horizontally or vertically and can support loads of up to 3,200 lb. Combined with its standard zinc plated mounting panel, the TS8 provides 15% more interior mounting space than unibody, NEMA-style enclosures. Engineered with the challenges of real-world applications in mind, the TS8 can protect critical equipment in even the most demanding environments, reducing downtime and increasing productivity.

NEMA 12 Carbon Steel Freestanding, 1 Door		
Grainger No.	Rittal No.	Dimensions H x W x D
6RNH0	TS7502420NC1D	75 x 24 x 20
6RNH1	TS7503216NC1D	75 x 32 x 16
6RNH2	TS7503220NC1D	75 x 32 x 20
6RNH3	TS7504020NC1D	75 x 40 x 20
6VJL1	TS7504024NC1D	75 x 40 x 24
6VJL2	TS8303220NC1D	83 x 32 x 20
6VJL3	TS8304020NC1D	83 x 40 x 20
6VJL4	TS8303224NC1D	83 x 32 x 24
6VJL5	TS8304024NC1D	83 x 40 x 24
6VJL6	TS9003224NC1D	90 x 32 x 24
6VJL7	TS9004020NC1D	90 x 40 x 20
6VJL8	TS9004024NC1D	90 x 40 x 24

NEMA 12 Carbon Steel Freestanding for Disconnect Applications, 1 Door		
Grainger No.	Rittal No.	Dimensions H x W x D
6VJN6	TS7503216XC1D	75 x 32 x 16
6VJN7	TS7503220XC1D	75 x 32 x 20
6VJN8	TS7504020XC1D	75 x 40 x 20
6VJN9	TS8303220XC1D	83 x 32 x 20
6VJP0	TS8303224XC1D	83 x 32 x 24
6VJP1	TS8304020XC1D	83 x 40 x 20
6VJP2	TS8304024XC1D	83 x 40 x 24
6VJP3	TS9003224XC1D	90 x 32 x 24
6VJP4	TS9004020XC1D	90 x 40 x 20
6VJP3	TS9003224XC1D	90 x 32 x 24
6VJP4	TS9004020XC1D	90 x 40 x 20



NEMA 12 Carbon Steel Freestanding, 2 Door		
Grainger No.	Rittal No.	Dimensions H x W x D
6VJL9	TS7504720NC2D	75 x 47 x 20
6VJN0	TS7506320NC2D	75 x 63 x 20
6VJN1	TS7507120NC2D	75 x 71 x 20
6VJN2	TS7507124NC2D	75 x 71 x 24
6VJN3	TS8307120NC2D	83 x 71 x 20
6VJN4	TS8307124NC2D	83 x 71 x 24
6VJN5	TS9004720NC2D	90 x 47 x 20

NEMA 12 Carbon Steel Freestanding for Disconnect Applications, 2 Door		
Grainger No.	Rittal No.	Dimensions H x W x D
6VJP5	TS7506320XC2D	75 x 63 x 20
6VJP6	TS7507120XC2D	75 x 71 x 20
6VJP7	TS7507124XC2D	75 x 71 x 24
6VJP8	TS8307120XC2D	83 x 71 x 20
6VJP9	TS8307124XC2D	83 x 71 x 24



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Rittal Corporation – Freestanding Industrial Enclosures

Accessories		
Grainger No.	Rittal No.	Description
6UUN7	FDS1212C	12"H x 12"W Fold-Down Shelf
6UUN8	FDS1818C	18"H x 18"W Fold-Down Shelf
6UUN2	9968111	Enclosure Lights, 18"L, 15W, 120V, 60Hz
6UUN3	9968112	Enclosure Lights, 24"L, 18W, 120V, 60Hz
6UUN4	4155500	Univ. Light With Motion Sensor, 26W
6UUN5	4315150	118" Power Cable For Univ. Light
6UUN6	4315450	24" Through-Wiring For Univ. Light



For more information, contact your Grainger Representative or visit Grainger.com®