

NEW! ReadySpace™ Storage System

Ready, Set, Organize!

Quickly Create Organized Storage Space Virtually Anywhere!

Designed for hospitals, labs and medical offices, ReadySpace is a high quality, steel louvered rack and panel system that interworks with our colorful selection of AkroBins®.

All ReadySpace panels have a clean, sleek look with a durable white, powder-coated finish. The ReadySpace Storage System is available in three options: **Wall Unit** – can be hung on a wall to maximize floor space; **Bench Unit** – for use on a desk or countertop; and a **Mobile Floor Unit** – for easy mobile or stationary storage, featuring lockable casters and optional Leveling Feet. Set up and installation is quick and easy.

- Create a neat, attractive storage space in any environment
- Customer-friendly appearance
- Keep supplies organized and readily available
- Utilizes valuable floor or wall space that might otherwise be wasted
- Use with **AkroBins** – available in a wide variety of sizes and colors for color coding, product protection and labeling
- Bench and Mobile Floor Units can double as a mobile privacy wall!

ReadySpace Packages Make Organization Easy!

- Wall, Bench or Mobile Floor Units can be purchased alone or with AkroBins
- Pre-configured packages are available or create your own custom system!



**Wall Unit
Model 30536**
37 1/2" x 1 3/4" x 25 3/8"



**Bench Unit
Model 98536**
37 3/4" x 12" x 26 3/8" (Single-Sided)
37 3/4" x 22 1/2" x 26 3/8" (Double-Sided)

**Mobile Floor Unit
Model 30553**
24 5/8" x 23" x 52"

Wall Unit includes a wall mounting bracket for easy installation



Wall Unit
Model 30536



Bench Unit
Model 98536



Mobile Floor Unit
Model 30553

ReadySpace Wall Unit

- Organize items and utilize valuable wall space
- Bins can be rearranged as needed
- Use alone or side-by-side with additional Wall Units
- Easy installation – wall bracket included!

ReadySpace Bench Unit

- Optimizes workspace areas
- Available as single or double-sided unit
- Two-piece base allows placement against or away from wall
- Easily moved from one work area to another

ReadySpace Mobile Floor Unit

- Organize and transport supplies and products where needed
- Convenient option for mobile storage
- Perfect for "high demand" items
- Panel locks into posts on base easily and without tools
- Standard with four lockable casters
- Leveling Feet (sold separately) make the Mobile Floor Unit stationary



Leveling feet available for Mobile Floor Unit



ReadySpace Wall Unit

Model Number	Description (L x W x H)	Unit Weight Capacity	No. of Ctns	Ship Weight (lbs.)	Qty. Bins
30536	37 1/2" x 1 3/4" x 25 3/8"	50 lbs.	1	35	N/A
30536210S	Unit with 30210STONE bins		3	45	48
30536220S	Unit with 30220STONE bins		3	51	48
30536230S	Unit with 30230STONE bins		3	55	24
30536235S	Unit with 30235STONE bins		3	55	12
30536320S	Unit with 30320STONE bins		2	47	4

ReadySpace Bench Unit (Assemble as Single or Double-Sided)

98536	37 3/4" x 12" x 26 3/8" (Single-Sided)	50 lbs.	1	51	N/A
	37 3/4" x 22 1/2" x 26 3/8" (Double-Sided)	100 lbs.			N/A

ReadySpace Single-Sided Bench Unit Kits

98536210SS	Unit with 30210STONE bins		3	61	48
98536220SS	Unit with 30220STONE bins		3	67	48
98536230SS	Unit with 30230STONE bins		3	71	24
98536235SS	Unit with 30235STONE bins		3	71	12
98536320SS	Unit with 30320STONE bins		2	63	4

ReadySpace Double-Sided Bench Unit Kits

98536210SD	Unit with 30210STONE bins		5	71	96
98536220SD	Unit with 30220STONE bins		5	83	96
98536230SD	Unit with 30230STONE bins		5	91	48
98536235SD	Unit with 30235STONE bins		5	91	24
98536320SD	Unit with 30320STONE bins		3	75	8

ReadySpace Mobile Floor Unit

30553	24 5/8" x 23" x 52"	150 lbs.	1	87	N/A
30553210S	Unit with 30210STONE bins		6	112	120
30553220S	Unit with 30220STONE bins		6	112	120
30553230S	Unit with 30230STONE bins		6	137	60
30553235S	Unit with 30235STONE bins		6	137	30
30553LF	Leveling Feet for Floor Unit		N/A	.5	N/A

AkroBins

- Molded of high-impact polypropylene, AkroBins are unaffected by weak acids and alkalis
- Sturdy, one-piece construction is water, rust and corrosion-proof
- Guaranteed not to crack or break under normal load conditions as stated in our 1-year limited warranty
- Autoclavable up to 250°F
- Available in 6 colors: Red, Yellow, Blue, Stone, Green and Black

AkroBins

Model No.	Outside Dimensions						Inside Dimensions						Bin Load Capacity On Rack**	Ctn. Qty.		
	Inches		mm		Inches		mm		mm							
	L	W	H	L	W	H	L	W	H	X	L	W	H	X		
30210	5 3/8	4 1/8	3	137	105	76	4 3/4	3 7/16	2 13/16	4	120	87	71	102	10 lbs	24
30220	7 3/8	4 1/8	3	187	105	76	6 3/4	3 7/16	2 13/16	6	171	87	71	152	10 lbs	24
30230	10 7/8	5 1/2	5	276	140	127	10 1/4	4 3/8	4 3/4	9	260	111	121	229	30 lbs	12
30235	10 7/8	11	5	276	279	127	10 1/4	10	4 3/4	9	260	254	121	229	50 lbs	6
30250	14 3/4	16 1/2	7	375	419	128	14	14 3/4	6 3/4	12	356	375	171	305	75 lbs	6
30320	8 5/8	33	5	187	819	76	6 5/8	31 3/4	4 3/16	5 7/8	153	807	106	149	80 lbs	4

One color per carton: Specify Red, Blue, Yellow, Stone, Green or Black. Order in carton quantities.

** CAUTION: When using bins with hanging systems, do not exceed the weight capacity for the rack which may be less than the total sum of bin capacities.



1293 South Main Street, Akron, Ohio 44301 • Tel: 800.253.2467 • Fax: 330.761.6348 • sales@akro-mils.com

In Canada: 8030 Torbram Road, Brampton, Ontario L6T 3T2 • Tel: 877.877.9680 • Fax: 905.791.4084 • sales@akro-milscanada.com

Visit our website: www.akro-mils.com or www.akro-milscanada.com