



More Cutting Power.

High Leverage Lineman's Pliers

For more powerful cutting and gripping when working in harsh conditions, the 9 1/4" High Leverage Lineman's Pliers from KNIPEX is a tool you can count on.

Key Features:

- cuts hard and soft wire, ACSR, bolts, screws and nails
- features a high leverage construction that requires 40% less effort compared to conventional Lineman's pliers
- a cross hatch gripping zone in the jaws enables strong gripping and pulling
- includes an additional gripping zone below the joint for powerful leverage and squeezing performance.
- ergonomically optimized handle shape allows firm, comfortable contact for the hand
- available with Non-Slip, Comfort Grip, or Insulated handles



	Part #	UPC #	Description	Capacity med./hard	hard	Handle Style	oz.
	09 01 240 SBA	843221000455	9 1/4" High Leverage Lineman's Pliers	3/16"	1/8"	Non-Slip Grip	15
	09 02 240 SBA	843221000462	9 1/4" High Leverage Lineman's Pliers	3/16"	1/8"	Comfort	16.5
	09 08 240 SBA	843221000479	9 1/4" High Leverage Lineman's Pliers	3/16"	1/8"	Insulated	17

Cross hatch serrations for a great grip

New England style head

Induction hardened cutting edges cut extra hard wire including ACSR and bolts

Smooth, high leverage rivet

Serrated gripping and crushing area

Comfort Grip handles for excellent hand contact and fatigue-reducing operation. Also available with Non-Slip Grip and Insulated handles.



High-Leverage Lineman's Pliers – Crimper and Fish Tape Puller

Cut a wire – Pull a fish tape – Crimp a terminal.

All of the features of the High Leverage Lineman's Pliers plus:

- built-in crimper for insulated and non-insulated terminals
- built-in fish tape puller grips any flat fish tape
- available with Non-Slip Grip or Comfort Grip handles

	Part #	UPC #	Description	Capacity med./hard	hard	Handle Style	oz.
	09 11 240 SBA	843221008963	9 1/4" Lineman's – Crimper, Fish Tape Puller	3/16"	1/8"	Non-Slip Grip	15
	09 12 240 SBA	843221008970	9 1/4" Lineman's – Crimper, Fish Tape Puller	3/16"	1/8"	Comfort	16.5

Cross hatch serrations enable strong gripping and pulling

New England style head

Induction hardened cutting edges cut extra hard wire including ACSR and bolts

Smooth, high leverage rivet

Fish tape puller in backside

Terminal crimper

Serrated crimping area

Non-Slip Grip handles



Visit www.knipex-tools.com for information on other KNIPEX products.



2035 S. Arlington Heights Rd., Suite 110
Arlington Heights, IL 60005

847.398.8520
847.398.8526 (fax)

www.knipex-tools.com

