

PIG® Extra-Duty Absorbent Mat Roll

#MAT2004 - Medium-weight • 32" x 150'



With additional top and bottom layers for extra toughness, PIG Extra-Duty Mat is highly abrasion resistant so it won't rip, tear, or fray.

- Special spunbond outer layers resist ripping and fraying from wiping rough surfaces or parts that would shred conventional mats
- No matter how you use it, this mat builds on the proven eight-layer, 100% polypropylene construction of PIG Mat, the strongest mat on the market!
- Exclusive dimple pattern speeds wicking of liquid throughout mat for faster, easier cleanup
- Highly absorbent, fine-fiber construction won't leave behind liquids or fiber residue
- Absorbs most common industrial liquids - oils, water, solvents, coolants and more; absorbs everything, works everywhere; that's why more plants worldwide use PIG Mat than any other brand
- Absorbed leaks and drips blend right in; dark gray color hides grime so mat stays on the job longer
- Low-lint for wiping rough parts or equipment and for cleaning in paint booth applications; also great for lining benches for rough or sharp parts
- Flame-resistant material won't burn immediately like cellulose mats; melts when exposed to high heat while on the job
- Rolls are perforated every 10"; easy to tear to size, use only what you need
- Medium-weight construction offers great performance for everyday tasks and cleanups

Always in stock. Ships within 24 hours.



New Pig

By Phone:
1-855-493-HOGS

Online:
newpig.com

Email:
hothogs@newpig.com

One Pork Avenue • Tipton PA 16684-0304

© 2014 New Pig Corporation. All rights reserved.
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: MAT2004 - Pg 1 of 2

MAT2004 Specifications

Color:	Dark Gray
Dimensions:	32" W x 150' L
Mat Weight:	Medium-weight
Fluids Absorbed:	Oils, Coolants, Solvents & Water
Recycled Content:	40% Recycled Content
Absorbency:	Up to 27 gal. per bag
Absorbency per:	Up to 27 gal. per roll
Dispenser:	No
Perforated:	Every 10" Lengthwise & Centered Widthwise
Poly-Backing:	No
UV Resistant:	No
Sold as:	1 roll per bag
Weight:	18.422 lbs.
# per Pallet:	24
Composition:	100% Polypropylene
UNSPSC:	47131901

Technical Information

Warnings & Restrictions:

There are no known warnings and restrictions for this product.

Regulations and Compliance:

29 CFR 1910.22(a)(2) - Floors in the workplace should be, "maintained in a clean and, so far as possible, a dry condition."

Technical Documents:

(Available at newpig.com)

Product Data Sheet (PDS)

Safety Data Sheet (SDS)

Chemical Compatibility (CCG)



MAT2004 Metric Equivalent

Dimensions:	81.3cm W x 46m L
Absorbency:	Up to 102.2 L per bag
Absorbency per:	Up to 102.2 L per roll
Weight:	8.4 kg



New Pig

By Phone:
1-855-493-HOGS

Online:
newpig.com

Email:
hothogs@newpig.com