

PIG® Poly-Back Brown Oil-Only Absorbent Mat Roll

#MAT598 - Heavy-weight • 31" x 75'



Lasts 2x longer than ordinary mats for fewer change-outs, while only absorbing oil and fuels, NOT water. Loves oil. Hates water. Brown color looks cleaner, longer.

- Brown color looks cleaner, longer, by blending in with most environments for both indoor and outdoor use; hides grime, so mat stays on the job longer
- Eight layers of 100% polypropylene are thermally bonded to make PIG Mat the strongest mat on the market; won't rip, tear or fray even when saturated
- Exclusive dimple pattern speeds wicking of liquid throughout mat for faster, easier cleanup
- Highly absorbent, fine-fiber construction won't leave behind liquids or fiber residue
- Absorbs oil and fuels, NOT water
- Floats to clean up spills on water
- Can be wrung out and incinerated after use to reduce waste or for fuels blending
- Flame-resistant material won't burn immediately like cellulose mats; melts when exposed to high heat while on the job
- 5-mil poly backing prevents absorbed liquids from reaching floors or counters and provides added traction for safe footing
- Place over a spill with poly-back side up to suppress potentially harmful, flammable or irritating vapors
- Rolls are ideal for covering large areas and soaking up leaks and overspray
- Heavy-weight construction is highly durable and absorbent for demanding tasks and large-volume cleanups

Always in stock. Ships within 24 hours.



By Phone:
1-855-493-HOGS

Online:
newpig.com

Email:
hothogs@newpig.com

New Pig

One Pork Avenue • Tipton PA 16684-0304

© 2014 New Pig Corporation. All rights reserved.
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: MAT598 - Pg 1 of 2

MAT598 Specifications

Color:	Brown
Dimensions:	31" W x 75' L
Mat Weight:	Heavy-weight
Fluids Absorbed:	Oil-based Liquids But Not Water
Absorbency:	Up to 22.6 gal. per bag
Absorbency per:	Up to 22.6 gal. per roll
Dispenser:	No
Perforated:	No
Poly-Backing:	Yes
UV Resistant:	No
Sold as:	1 roll per bag
Weight:	19 lbs.
# per Pallet:	24
Composition:	Mat - 100% Polypropylene Barrier - 100% Polypropylene
UNSPSC:	47131901

Technical Information

Warnings & Restrictions:

There are no known warnings and restrictions for this product.

Regulations and Compliance:

29 CFR 1910.22(a)(2) - Floors in the workplace should be, "maintained in a clean and, so far as possible, a dry condition."

Technical Documents:

(Available at newpig.com)
Product Data Sheet (PDS)
Safety Data Sheet (SDS)



MAT598 Metric Equivalent

Dimensions:	78.7cm W x 23m L
Absorbency:	Up to 85.5 L per bag
Absorbency per:	Up to 85.5 L per roll
Weight:	8.6 kg



By Phone:
1-855-493-HOGS

Online:
newpig.com

Email:
hothogs@newpig.com

New Pig

One Pork Avenue • Tipton PA 16684-0304
© 2014 New Pig Corporation. All rights reserved.
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: MAT598 - Pg 2 of 2