



Rittal – The System.

Faster – better – everywhere.

Rittal Corporation – Junction Box Enclosures

Rittal junction box enclosures provide the protection, flexibility and value that translate to reliable and lasting solutions for today's intensive "return on investment" business approach. Rittal engineers its junction boxes to be the best available anywhere in the world when it comes to form, function and value for the money. Readily available from Grainger in all of the most popular sizes, protection categories and configurations, unique design features like foamed-in-place gasketing and knife-edge perimeters are examples of Rittal's ability to provide innovative, durable, quality enclosure solutions at affordable prices.

NEMA 4 KL Carbon Steel Screw Cover Junction Box			KL Mounting Panel (Not Included)		
Grainger No.	Rittal No.	H x W x D	Grainger No.	Rittal No.	H x W x D
5ENA5	1514.510	6 x 6 x 3	6VJU6	1560.700	5 x 5
5ENC0	1515.510	6 x 12 x 3	6VJU8	1561.700	11 x 5
5ENC5	1516.510	8 x 8 x 3	6VJU7	1562.700	7 x 7
5END0	1517.510	8 x 12 x 3	6VJU9	1563.700	11 x 7
5END2	1504.510	8 x 16 x 5	6VJV1	1564.700	15 x 7
5ENF2	1507.510	12 x 12 x 5	6VJV0	1567.700	11 x 11



NEMA 4X KL 304 Stainless Steel Screw Cover Junction Box			KL Mounting Panel (Not Included)		
Grainger No.	Rittal No.	H x W x D	Grainger No.	Rittal No.	H x W x D
5ENA6	1521.010	6 x 6 x 3	6VJU6	1560.700	5 x 5
5ENC1	1522.010	6 x 12 x 3	6VJU8	1561.700	11 x 5
5ENC6	1523.010	8 x 8 x 3	6VJU7	1562.700	7 x 7
5END1	1524.010	8 x 12 x 3	6VJU9	1563.700	11 x 7
5END3	1525.010	8 x 16 x 5	6VJV1	1564.700	15 x 7
5ENF3	1526.010	12 x 12 x 5	6VJV0	1567.700	11 x 11



Accessories		
Grainger No.	Rittal No.	Description
5AAJ1	1590.000	Wallmounting Brackets, Sheet Steel, Zinc-plated, Passivated
5AAJ2	1594.000	Wallmounting Brackets, 304 Stainless Steel

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



FRIEDHELM LOH GROUP

Rittal Corporation – Junction Box Enclosures



NEMA 4 & 12 JB Carbon Steel Hinge Cover Junction Box		
Grainger No.	Rittal No.	HxWxD
5EMZ9	JB040403HC	4x4x3
5ENA2	JB060403HC	6x4x3
5ENA7	JB060604HC	6x6x4
5ENC2	JB080604HC	8x6x4
5ENC7	JB080804HC	8x8x4
5END4	JB100804HC	10x8x4
5ENE4	JB121005HC	12x10x5
5END8	JB100806HC	10x8x6
5ENE1	JB101006HC	10x10x6
5ENE7	JB121006HC	12x10x6
5ENF5	JB121206HC	12x12x6
5AAA0	JB141206HC	14x12x6
5AAA9	JB161406HC	16x14x6
5ENE9	JB121008HC	12x10x8
5AAC1	JB161408HC	16x14x8

Note: Zinc panel included, except in 4x4x3 junction box

NEMA 4X JB 304 Stainless Steel Hinge Cover Junction Box		
Grainger No.	Rittal No.	HxWxD
5ENA0	JB040403H4	4x4x3
5ENA3	JB060403H4	6x4x3
5ENA8	JB060604H4	6x6x4
5ENC3	JB080604H4	8x6x4
5ENC8	JB080804H4	8x8x4
5END5	JB100804H4	10x8x4
5END9	JB100806H4	10x8x6
5ENE2	JB101006H4	10x10x6
5ENE8	JB121006H4	12x10x6
5ENF6	JB121206H4	12x12x6
5AAA1	JB141206H4	14x12x6
5AAC0	JB161406H4	16x14x6
5ENF0	JB121008H4	12x10x8
5AAC2	JB161408H4	16x14x8

Note: Zinc panel included, except in 4x4x3 junction box

NEMA 4X JB 316L Stainless Steel Hinge Cover Junction Box		
Grainger No.	Rittal No.	HxWxD
5ENA1	JB040403H6	4x4x3
5ENA4	JB060403H6	6x4x3
5ENA9	JB060604H6	6x6x4
5ENC4	JB080604H6	8x6x4
5ENC9	JB080804H6	8x8x4
5END6	JB100804H6	10x8x4
5END7	JB100806H6	10x8x6
5ENE0	JB101006H6	10x10x6
5ENE6	JB121006H6	12x10x6
5ENF4	JB121206H6	12x12x6
5ENG0	JB141206H6	14x12x6
5AAA8	JB161406H6	16x14x6
5ENF1	JB121008H6	12x10x8
5AAC3	JB161408H6	16x14x8

Note: Zinc panel included, except in 4x4x3 junction box

Accessories		
Grainger No.	Rittal No.	Description
5AAJ1	1590.000	Wallmounting Brackets, Sheet Steel, Zinc-plated, Passivated
5AAJ2	1594.000	Wallmounting Brackets, 304 Stainless Steel
5AAJ5	2576.000	Thumb Turn Handle with Key Lock
5AAJ6	WMQTPLS6	Thumb Turn Handle, Padlockable, 316L Stainless Steel

For more information, contact your Grainger Representative or visit Grainger.com®