

## High-performance Photoluminescent Exit Signs

Safe Glow® exit signs feature handsome looks and industry leading photoluminescent performance. All **Safe Glow** exit signs are UL listed (35JP) to meet the requirements of UL 924, and meet all current NFPA and IBC code requirements. Non-electrical performance allows them to charge with ambient light. *To charge, a minimum of 5 foot-candles of unfiltered fluorescent light on the face of the sign is required at all times of building occupancy.*

### 5 Reasons Safe Glow's High Performance Photoluminescent Exit Signs Are Your Best Choice



- No electricity, No batteries, No maintenance, and No required annual testing
- UL 924 listing meets NFPA and IBC codes nationwide
- More photoluminescence and brighter performance for higher life safety
- Manufactured with quality components to ensure the highest photoluminescent performance
- Attractive design for any interiors, designed to stay that way over a 25 year life

#### Features:

- Meets all current building codes for high or low-level installation
- Non-radioactive and non-toxic
- Uses no electricity or batteries
- Charges using ambient light
- Glows for more than 12 hours
- No replacement parts or maintenance
- Minimizes time required for annual testing
- Average savings over LED exit signs is \$50 per sign, per year
- Easy installation
- In new construction, eliminates wiring, conduit, circuit breakers, and minimizes contractor costs for installation
- LEED points available

#### Specifications:

- UL 924 listed and meets UL 1994 performance guidelines
- Designed for indoor use
- Projected operating life - 25 years
- Warranty - 5 year limited warranty

## Exit Sign Mounting Options



**Flush Mount** – to mount signs flush to the wall.



**Hard Surface Mount** – to mount signs from the top, bottom or side (flag) on any hard surface where screw anchors can be installed.



**T-bar Mount** – Comes with clips for mounting on supported 1" T-bar.

## High-performance Photoluminescent Exit Signs

Safe Glow® High Performance Photoluminescent Exit Signs are UL 924 listed and code-compliant for high or low-level mounting. Requires 5 foot candles of fluorescent light for charging (see building code requirements). All have a viewing distance of 50 ft.

Dimensions: L 12.31" x H 9.5" x T.25"

Weight: 1 lb. 11 oz.



Model	Color	Legend	Mounting
15F263	Green	Exit	Flush/Wall
15F265	Green	Exit	Hard Surface
15F264	Green	Exit	T-bar



Model	Color	Legend	Mounting
15F260	Red	Exit	Flush/Wall
15F262	Red	Exit	Hard Surface
15F261	Red	Exit	T-bar

## High Performance Photoluminescent Exit Signs - Directional

Dimensions: L 14.625" x H 9.5" x T .25"

Weight: 1 lb. 15 oz.



Model		Color	Legend	Mounting
Single* Sided	Double** Sided			
15F273		Green	<Exit	Flush/Wall
15F275	15F269	Green	<Exit	Hard Surface
15F274	15F268	Green	<Exit	T-bar



Model		Color	Legend	Mounting
Single* Sided	Double** Sided			
15F279		Green	Exit>	Flush/Wall
15F281	15F269	Green	Exit>	Hard Surface
15F280	15F268	Green	Exit>	T-bar



Model		Color	Legend	Mounting
Single* Sided	Double** Sided			
15F270		Red	<Exit	Flush/Wall
15F272	15F267	Red	<Exit	Hard Surface
15F271	15F266	Red	<Exit	T-bar



Model		Color	Legend	Mounting
Single* Model	Double** Sided			
15F276		Red	Exit>	Flush/Wall
15F278	15F267	Red	Exit>	Hard Surface
15F277	15F266	Red	Exit>	T-bar

\* **Single Sided Signs** – Single sign with “exit” displayed on one side only

\*\* **Double Sided Signs** – Back to back signs connected together with “exit” displayed on both sides

## High Performance Photoluminescent Exit Signs - Bi-directional

Dimensions: L 16.91" x H 9.5" x T .25"

Weight: 2 lbs. 4 oz.



Model		Color	Legend	Mounting
Single* Sided	Double** Sided			
15F287		Green	<Exit>	Flush/Wall
15F290	15F291	Green	<Exit>	Hard Surface
15F288	15F289	Green	<Exit>	T-bar



Model		Color	Legend	Mounting
Single* Sided	Double** Sided			
15F282		Red	<Exit>	Flush/Wall
15F285	15F286	Red	<Exit>	Hard Surface
15F283	15F284	Red	<Exit>	T-bar

## “Not an Exit” Signs

Safe Glow recommends 5 foot candles of fluorescent light for charging our “Not an Exit” signs.

Dimensions: L 12.31" x H 9.5" x T.25"

Weight: 1 lb. 11 oz.



Model	Color	Legend	Mounting
15F295	Green	Not an Exit	Flush/Wall
15F297	Green	Not an Exit	Hard Surface
15F296	Green	Not an Exit	T-bar



Model	Color	Legend	Mounting
15F292	Red	Not an Exit	Flush/Wall
15F294	Red	Not an Exit	Hard Surface
15F293	Red	Not an Exit	T-bar