



L40 Wipers

Product Information

Code	Color	Ply	Sheet Size	Put-Up	Sheets/Pack	Packs/Case	Sheets/Case
05740	Blue	1	16.4" x 9.8"	POP-UP*	100	9	900
05790	White	1	16.4" X 9.8"	POP-UP*	100	9	900
03046	White	1	10" X 9.8"	POP-UP*	90	9	810
05600	White	1	12.5" x 12"	1/4 Fold	56	12	672
05701	White	1	12.5" x 12"	1/4 Fold	56	18	1008
05776	Blue	1	12.5" x 12"	1/4 Fold	56	12	672
05027	White	1	11" x 10.4"	Small Roll	70	24	1680
05796	White	1	10" x 13.2"	Center Pull Roll	200	0	400
05007	White	1	12.5" x 13.4"	Jumbo Roll	750	1	750

Physical Properties

The following are current, subject to change at any time without notice. Physical property data is as produced; subsequent storage conditions and the age of the product, which are beyond Kimberly-Clark's control, may affect the properties of the product as received. Test results of competitive product are single sample of the product provided by the customer.

Property	Target	Testing Method
Water Capacity (g/4"x4")	5.5	STM 2401
Oil Capacity (g/4"x4")	4.6	STM 2401
Bulk, 24 sheets (mils)	570	STM 3007
Tensile Strength MD Wet (g/3 in.)	2800	STM 5500
Tensile Strength CD Wet (g/3 in.)	1550	STM 5500
Tensile Strength CD Dry (g/3 in.)	2200	STM 5500



Workmanship Requirements

Wipers shall be made in accordance with reasonable industry practice with respect to holes, tears, wrinkles, cleanliness, odors and foreign materials or dirt. Edges shall be cleanly cut.

Kimberly-Clark warrants that its products (1) comply with K-C's standard specifications as of the delivery date to K-C's authorized distributors/direct purchasers and are warranted for the following periods from end user's date of purchase (verified by valid sales receipt) (a) five years for Balder Technology auto darkening filters; (b) two years for all other auto darkening filters; and (c) one year for powered air purifying respirators; (2) comply with all K-C labeling representations; and (3) are manufactured in compliance with all applicable federal, state, and local laws in effect at the time and place of manufacture of the products. THIS WARRANTY IS IN LIEU OF ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. K-C is not liable for any kind of special, incidental, or consequential damages. K-C's liability for breach of contract, tort or other cause of action shall not exceed the product purchase price. Purchasers and users are deemed to have accepted the above warranty and limitation of liability, and cannot change the terms by verbal agreement or by any writing not signed by K-C. To the extent required by applicable law, K-C does not limit its liability for death/injury resulting from K-C's negligence.