



jalas® GRAN PREMIO 1808 ICE TRACK

ASTM F2413-18 M/I/C/SD 35/PR EN ISO 20345:2011 S3, SRC, CI, HRO

Learn more

FOR EXTREME COLD CONDITIONS

A triple-lined lace-up winter safety boot with highest protection (S3) designed for very cold environments. The PU-coated leather upper protects feet and keeps them warm and comfortable all day long. The nitrile outer sole is both oil and heat-resistant and gives excellent grip, while JALAS® aluminium toe cap, plasma-treated textile puncture protection and double impact protection zones in PORON® XRD® help prevent injuries.

CHARACTERISTICS

- Highest level of protection
- Excellent grip
- Perfect fit
- Extra comfortable
- Extremely warm
- Excellent shock absorption

FUNCTIONS

- ProNose toe reinforcement
- Wide fit
- Heat-resistant outsole
- Oil-resistant outsole
- Anti-static properties
- Bellows tongue
- Padded boot shaft
- Pull loops
- Zipper
- Water repellent
- Double shock absorption zones
- Conforms with IEC 61340-5-1 (ESD)

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Toe injuries, Nail penetration, Antistatic, Contact with cold

PRIMARY ENVIRONMENTS OF USE

Outdoors, Environments with risk for outsole penetration, Cold environments, Harsh environments

SPECIFICATION

TYPE Safety footwear, Boots/Ankle boots
CATEGORY Cat. II
NAIL PROTECTION MATERIAL Plasma-treated composite (PTC) textile
FITTING Wide
COLLECTION Gran Premio
UPPER MATERIAL PU-coated leather
PRONOSE MATERIAL PU
TOECAP MATERIAL Aluminium
LINING MATERIAL Aluminium foil, Polyester fur, Thinsulate™
INSOLE JALAS 8245 FX2 ThermAL
INNERSOLE MATERIAL Textile, Aluminium foil, Soft EVA, Polyester-based conductive thread, Merino wool, Double shock absorption zones in PORON® XRD®
MIDSOLE MATERIAL PU midsole
OUTSOLE MATERIAL Nitrile rubber outsole
FASTENING Laces, Zipper
SHOELACES LENGTH 160 cm
COLOUR Black
NET WEIGHT, (SIZE 42) 1.69 kg

COMPLIANCE

CE Cat. II

EAC TP TC 019:2011

ASTM F2413-18
M/I/C/SD 35/PR

EN ISO 20345:2011
S3, SRC, CI, HRO

FEATURES

- Anti-static properties
- Ergothan Shock Absorption System
- ESD
- Aluminium toecap
- Oil-resistant outsole
- ProNose toe reinforcement
- Nail protection in plasma-treated composite (PTC) textile
- Wide fit
- Heat-resistant outsole
- Water repellent
- Winter model
- Zipper

SIZE				ARTICLE NUMBER	EAN
EU	UK	US M	US W		
36	3	4	5	1808-36	6408487442117
37	4	5	6	1808-37	6408487442124
38	5	5.5	6.5	1808-38	6408487442131
39	6	6.5	7.5	1808-39	6408487442148
40	6.5	7.5	8.5	1808-40	6408487442155
41	7	8	9	1808-41	6408487442162
42	8	9	10	1808-42	6408487442179
43	9	9.5	11	1808-43	6408487442186
44	10	10.5	11.5	1808-44	6408487442193
45	10.5	11	12.5	1808-45	6408487442209
46	11	12	13	1808-46	6408487442216
47	12	13	14	1808-47	6408487442223
48	13	13.5	14.5	1808-48	6408487442230

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.